

2 Port USB VGA KVM Switch with File Transfer and PIP

Product ID: SV231UAF



The SV231UAF 2 Port USB VGA KVM Switch with File Transfer and PIP offers control of 2 computers, using a single keyboard, mouse and monitor. The KVM switch offers a compact design, saving desk space in addition to saving the cost of purchasing separate peripherals for each computer.

The KVM Switch features a picture-in-picture function (Windows only) that allows you to look at the other connected system, while still working on the one in focus. The switch also offers a data link feature that lets you drag and drop files or folders between your connected Windows computers, for quick and easy data transfers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for business users that operate their laptops at multiple locations where files need to be shared between laptop and PC
- Useful for call centers, help desks, education environments, where files are often shared between a multiple PCs
- Can be connected in a server room to support easy file transfers between the connected server and the technician or admin's laptop
- Control any two USB VGA computers with one keyboard, mouse, monitor and set of speakers

Features

- Picture in Picture (PIP) function allows drag and drop file transfers between two computers

- Supports switching via manual push-button, hot-key command or software
- Supports Copying and Pasting text between connected systems
- USB powered - No external adapter required
- Access multiple PCs with one set of Keyboard, Mouse, Monitor and Audio peripherals
- Kit includes PC connection cables
- High resolution support (up to 2048x1536)
- Compatible with USB 1.1/2.0 Specifications
- Supports DDC, DDC2, and DDC2B
- Space-saving compact design

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048x1536
Wide Screen Supported	Yes
Maximum Number of	1



Users	
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position) USB Type-A (4 pin) USB 2.0 VGA (15 pin, High Density D-Sub)
Host Connectors	VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	Windows 8 (32/64), 7 (32/64), Vista (32/64), XP (32/64)
------------------	---

Special Notes / Requirements

Note	File transfer not supported on Mac OS
------	---------------------------------------

Indicators

LED Indicators	Green - Port selection indicator
----------------	----------------------------------

Power

Power Consumption (In Watts)	0.97 W
------------------------------	--------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	90% RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	1 x 1.2m (4ft) 3-in-1 VGA, USB and Audio Host Cable 1 x 1.8m (6ft) 3-in-1 VGA, USB and Audio Host Cable
Product Length	4.3 in [11 cm]
Product Width	4.3 in [11 cm]

Product Height	1.1 in [27 mm]
Product Depth	2.6 in [65 mm]
Weight of Product	3.5 oz [100 g]

Packaging Information

Package Length	10.6 in [26.9 cm]
Package Width	6.5 in [16.5 cm]
Package Height	2.8 in [70 mm]
Shipping (Package) Weight	30.9 oz [876 g]

What's in the Box

Included in Package	Two port KVM unit
	PC Connection Cables 1.8m (6ft)
	User Manual

****Product appearance and specifications are subject to change without notice.***

