

## 4 Port Black USB KVM Switch Kit with Cables and Audio

**Product ID:** SV411KUSB



The SV411KUSB 4 Port USB KVM Switch Kit with Audio and Cables lets you control up to four USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes four, 4ft 4-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

## Features

- Cables (4 ft.) included
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048 x 1536 pixels
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

---

### Connector(s)



Console Interface(s)	VGA (15 pin, High Density D-Sub)
	USB Type-A (4 pin) USB 2.0
	3.5 mm Mini-Jack (3 Position)
Host Connectors	VGA (15 pin, High Density D-Sub)
	3.5 mm Mini-Jack (3 Position)

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

#### Power

Power Source	USB-Powered
--------------	-------------

---

#### Physical Characteristics

Color	Black
Material	Plastic
Cable Length	4.0 ft [1.2 m]
Product Width	3.7 in [95 mm]
Product Height	1.0 in [25 mm]
Product Depth	2.4 in [61 mm]
Weight of Product	6.7 oz [189 g]

---

#### Packaging Information

Package Length	8.3 in [21 cm]
Package Width	7.1 in [18 cm]
Package Height	5.7 in [14.5 cm]
Shipping (Package) Weight	3.1 lb [1.4 kg]

---

#### What's in the Box

Included in Package	4 Port KVM Switch
	4ft. VGA USB KVM Cable



4ft. Audio Cable (3.5mm speaker/mic)

Instruction Manual

Driver CD

---

***\*Product appearance and specifications are subject to change without notice.***

