

4 Port Black PS/2 KVM Switch

Product ID: SV431



This 4 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

Certifications, Reports and Compatibility

Applications

- Datacenter computer control
- Manufacturing computer control
- PC test/burn-in computer control

Features

- A dependable 3 year warranty provides peace of mind.


- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected system.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during power outage even if it loses power, retaining mouse control.
- Compact 1U rack height takes up very little cabinet or rack space
- Completely hot-pluggable feature allows you to add or remove keyboards, mice, monitors and even cascaded switches without powering down the switch or an attached computer
- A front panel pushbutton and status lights for each port make PC selection and switch status monitoring fast and easy
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- Works with notebook PCs and most varieties of scroll mice
- Can be cascaded to control up to 16 PCs
- Desktop or Rack-mountable (rackmount kit not included - see SV431RACK)
- Supports PCs requiring either PS/2 or serial mice (includes 2 serial adapters)
- Completely operating system independent. No software or drivers required

Hardware

Warranty	3 Years
U Height	1U
Audio	No
KVM Ports	4
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Optional
Cables Included	No
Daisy-Chain	Yes

Performance

DVI Support	No
-------------	----



IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	1920x1440
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	PS/2 (6 pin, Mini-DIN)
	VGA (15 pin, High Density D-Sub)
Host Connectors	PS/2 (6 pin, Mini-DIN)
	VGA (15 pin, High Density D-Sub)
Other Interface(s)	Mini-DIN (8 pin)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.2A
Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	0.6W

Physical Characteristics

Material	Steel
----------	-------



Product Width	8.6 in [21.9 cm]
Product Height	1.7 in [44 mm]
Product Depth	5.1 in [12.9 cm]
Weight of Product	5.3 lb [2.4 kg]

Packaging Information

Package Length	16.5 in [42 cm]
Package Width	3.5 in [88 mm]
Package Height	8.1 in [20.5 cm]
Shipping (Package) Weight	4.0 lb [1.8 kg]

What's in the Box

Included in Package	4 Port KVM Switch
	PS/2 to serial mouse adapters
	Sticky feet
	9V Power Adapter
	Hot key reference
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

