

4 Port Dual DVI USB KVM Switch with Audio & USB 2.0 Hub - TAA

Produkt ID: SV431DD2DUA



The SV431DD2DUA 4-port Dual DVI USB KVM Switch allows up to four PCs, each with dual DVI video outputs, to share two monitors, one microphone and set of speakers, one keyboard and one mouse as well as two other USB peripherals.

An ideal solution for graphic designers, CAD/CAM designers or educational and financial institutions, the dual view KVM Switch allows you to instantly switch back and forth between dual DVI display PCs at the touch of a button, while maintaining professional level video quality on both monitors. The dual DVI switch also features an integrated USB hub port that allows USB 2.0 peripherals such as thumb drives, external hard drives or web cams to be shared between attached systems - eliminating duplicate peripheral costs.

Please Note: While both DVI-I (analog mode) and DVI-D (digital only) are supported by the KVM, both source PCs should output the same signal type for proper switching. It is recommended wherever possible to use DVI-D cables across all PC to KVM and KVM to Console connections. Please contact technical support if you require assistance identifying your source.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

Certifikat, rapporter och kompatibilitet





Användning

- Four system control for single user workstations with dual head video cards, increasing user productivity in the office
- Control up to four dual display multimedia computers with a single set of console peripherals (Keyboard, Mouse, and two Monitors)
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications, and multiple screens
- Integrated USB 2.0 hub and Mic/Audio ports allow the user to have full multimedia control of two computers and share USB peripherals

Funktioner

- Front panel push-buttons and Hot-key functions for easy switching
- Supports resolutions up to 2048x1536 (Analog) and 1920x1200 (digital)
- USB 2.0 hub for peripheral sharing (Thumb drives, external hard drives, web cams, etc.)
- Audible tone confirms port switching
- Combined or independent switching of audio ports
- EDID retention - eliminates hassle when switching between computers as the KVM "remembers" monitor settings
- Supports all USB-capable operating systems (Windows 98e/SE/ME/2000/XP/Vista/7, Linux, Mac OS, etc.)
- TMDS compliant to support DDC2B emulation and HDCP for digital contents protection
- Status LED display for easy port status monitoring

Hårdvara

Garantipolicy	3 Years
Audio	Ja
KVM-portar	4

PC-gränssnitt	USB
PC-videotyp	DVI
Flera skärmar	Yes
Hyllmonterbar	Valfri
Medföljande kablar	Nej
Kedjekoppling	Nej

Prestanda

Skärmvisning (OSD) & stöd för snabbtangenter	Nej
DVI-stöd	Ja - Single Link
IP-kontroll	Nej
Hot-Key Selection	Ja
Maximal analog upplösning	2048x1536 @85Hz
Maximal digital upplösning	1920x1200 @60Hz
Maximalt antal användare	1
Stöd för portval	Tryckknapp och genvägskommandon
Medeltid mellan fel (MTBF)	140000 hours

Kontakt(er)

Konsolgränssnitt	2 - 3.5 mm minijack (3-polig)
	2 - DVI-I (29-stifts)
	4 - USB 2.0 Type-A (4 stift, 480 Mbps)
Värdkontakter	8 - 3.5 mm minijack (3-polig)
	8 - DVI-I (29-stifts)

4 - USB B (4-stifts)

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

Indikatorer

LED-indikatorer	1 - Green - Power
	4 - Green - Host Online, Red - Host Selected

Ström

Strömkälla	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.8A
Utpänning	12V DC
Utström	1.5A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	18

Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	90% RH

Utseende

Färg	Svart
Kabinettyp	Stål
Produktbredd	8.7 in [22 cm]
Produkthöjd	2.4 in [6 cm]
Produktdjup	5.1 in [130 mm]

	Produktvikt	2.8 lb [1.3 kg]
Förpackning		
	Förpackningsantal	1
	Paketets längd	11.6 in [29.5 cm]
	Paketets bredd	9.7 in [24.7 cm]
	Paketets höjd	3.4 in [86 mm]
	Fraktvikt (förpackning)	3.9 lb [1.8 kg]
Vad det är i lådan		
	Ingår i paketet	1 - 4-port dual DVI USB KVM
		4 - foot pads
		1 - universal power adapter (NA/EU/UK/AU)
		1 - instruction manual
Warranty Information		
	Warranty	3 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.