

4-port KVM Switch with Dual VGA - USB 2.0

Product ID: SV431DVG AU2A



This USB KVM lets you connect four computers, each with dual VGA outputs, to a dual-monitor workstation. You can switch the workstation between each computer, as well as two additional USB peripheral devices and 3.5mm speakers & microphone.

With support for two VGA video inputs and four different computers, this KVM switch maximizes productivity. Not only can you access multiple computers, but you can also use two VGA monitors on each computer streaming independent content to each display, which gives you the freedom to multitask and increase your productivity. The VGA ports support resolutions up to 1920x1200 for maximum screen viewing space.

Featuring dual video and support for your keyboard and mouse, along with a 2-port USB hub for additional peripheral devices, this KVM switch is perfect for accessing four separate systems using the same workstation. Support for your workstation plus two additional peripheral devices makes this KVM ideal for server control, simplifying access to multiple computer systems.

This 4-port KVM ensures effortless operation with intuitive hotkey control. It provides a simple yet comprehensive solution for switching between each connected computer and also supports manual operation using the easy-to-access buttons located on the front of the switch.

The SV431DVG AU2A is backed by a 2-year StarTech.com warranty and free lifetime technical support.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a [%product id="SV431RACK" text="1U Rackmount Bracket" %](sold separately) that turns this KVM into a rackmountable KVM.

Certifications, Reports and Compatibility



Applications

- Control four computers, each with dual head video cards, to increase your productivity at the office
- Work with multimedia applications such as video & photo editing
- Operate multiple computers in manufacturing lines
- Install in your server room, for multi-computer access

Features

- Maximum productivity with dual display and multi-computer access
- Hassle-free operation with hotkey and push-button switching
- Share your USB peripheral devices with built-in 2-port USB hub
- Supports resolutions up to 1920x1200
- 3.5mm speaker and microphone console support

Hardware	Warranty	2 Years
	Audio	Yes
	KVM Ports	4
	PC Interface	USB
	PC Video Type	VGA
	Number of Monitors Supported	2
	Rack-Mountable	Optional
	Cables Included	No
	Daisy-Chain	No
	Performance	On-Screen Display
DVI Support		No
IP Control		No
Hot-Key Selection		Yes
Maximum Analog Resolutions		1920 x 1200
Supported Resolutions		up to 1920 x 1200
Maximum Number of Users		1
Port Selection Support		Push Button and Hotkeys
MTBF		145000 hours
Connector(s)		Console Interface(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position)
Console Interface(s)	USB Type-A (4 pin) USB 2.0
Host Connectors	VGA (15 pin, High Density D-Sub)
Host Connectors	3.5 mm Mini-Jack (3 Position)
Host Connectors	USB B (4 pin)

Indicators	LED Indicators	PC Selection Indicators
	LED Indicators	Green - PC Detected
	LED Indicators	Green - Power
	LED Indicators	Red - PC Indicator

Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.8A
	Output Voltage	12V DC
	Output Current	1.5A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	18

Environmental	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	90% RH

Physical Characteristics	Color	Black
	Material	Steel
	Product Length	8.7 in [2.2 cm]
	Product Width	5.3 in [1.4 cm]
	Product Height	2.4 in [60 mm]
	Product Depth	5.1 in [1.3 cm]
	Weight of Product	2.7 lb [1.2 kg]

Packaging Information	Package Length	13.0 in [3.3 cm]
------------------------------	----------------	------------------



Package Width	10.0 in [2.6 cm]
Package Height	1.1 in [28 mm]
Shipping (Package) Weight	3.9 lb [1.8 kg]

What's in the Box	Included in Package	dual VGA USB KVM switch
	Included in Package	universal power adapter (NA / EU / UK / AU)
	Included in Package	instruction manual

****Product appearance and specifications are subject to change without notice.***

