

4 Port DVI USB KVM Switch with Audio and USB 2.0 Hub - TAA

Produkt-ID: SV431DVIUA



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Switches instantly between PCs

Merkmale

- USB keyboard and mouse support
- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- HDCP Compliant
- Independent/simultaneous audio & mic channel and PC port selection
- DVI interface technology supports digital video signal transmission
- Channel selection/Hub port control by front-panel push buttons

Hardware

Garantiebestimmungen 3 Years

Audio Ja

KVM-Ports 4

PC-Schnittstelle USB

PC-Videotyp DVI

Mehrfach-Monitor 1

Einbaufähig Optional

Mit Kabeln Nein

Reihenschaltung Nein

Leistung

OSD- & Schnell Tastenunterstützung
Nein

DVI-Unterstützung	Ja
IP-Steuerung	Nein
Hot-Key Selection	Nein
Max. Analogauflösungen	2560x1600 @ 60Hz
Max. Digitalauflösungen	1920x1200 @ 60/70Hz
Max. Anzahl von Benutzern	1
Portauswahlunterstützung	Drucktaste
MTBF	136000 Stunden

Steckverbinder

Konsolen-Schnittstelle(n)	2 - 3,5 mm Mini-Jack (3 Positionen)
	1 - DVI-I (29-polig)
	2 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
Hostanschlüsse	8 - 3,5 mm Mini-Jack (3 Positionen)
	4 - DVI-I (29-polig)
	4 - USB B (4-polig)
Andere Schnittstelle(n)	2 - USB 2.0 Typ-A (4 pin, 480Mbit/s)

Software

Betriebssystemkompatibilität	OS independent; No software or drivers required
------------------------------	---

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.4A

Ausgangsspannung	5 DC
Ausgangsstrom	2A
Polarität der Mittelspitze	Positiv
Steckertyp	N
	N
	N
Stromverbrauch	10

Umgebungsbedingungen

Betriebstemperatur	0°C to 40°C (32°F to 104°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0%~80%

Physische Eigenschaften

Farbe	Schwarz
Gehäusotyp	Stahl
Produktlänge	10.0 in [25.3 cm]
Produktbreite	1.8 in [4.5 cm]
Produkthöhe	4.5 in [11.5 cm]
Produktgewicht	2.3 lb [1.0 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	16.3 in [41.4 cm]
Paketbreite	8.5 in [21.5 cm]
Pakethöhe	3.6 in [9.1 cm]

Versandgewicht (Verpackung)	3.4 lb [1.5 kg]
--------------------------------	-----------------

Verpackungsinhalt

Im Paket enthalten	1 - 4 Port DVI KVM Switch
	4 - Rubber Feet
	1 - Power Adapter
	1 - User Manual

Garantieinformationen

Warranty	3 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.