

4 Port DVI USB KVM Switch with Audio and USB 2.0 Hub

Product ID: SV431DVIUA



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a [%product id="SV431RACK" text="1U Rackmount Bracket"](sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs

Features

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- Channel selection/Hub port control by front-panel push buttons
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous audio & mic channel and PC port selection
- USB keyboard and mouse support
- HDCP Compliant

Hardware	Warranty	3 Years
	Audio	Yes
	KVM Ports	4
	PC Interface	USB
	PC Video Type	DVI
	Number of Monitors Supported	1
	Rack-Mountable	Optional
	Cables Included	No
	Daisy-Chain	No
Performance	On-Screen Display	No
	DVI Support	Yes
	IP Control	No
	Hot-Key Selection	No
	Maximum Analog Resolutions	2560x1600 @ 60Hz 1920x1200 @ 60/70Hz
	Maximum Digital Resolutions	1
	Maximum Number of Users	Push Button
	Port Selection Support	136000 hours
	MTBF	
Connector(s)	Console Interface(s)	DVI-I (29 pin)
	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	Host Connectors	DVI-I (29 pin)
	Host Connectors	USB B (4 pin)

	Host Connectors	3.5 mm Mini-Jack (3 Position)
	Other Interface(s)	USB Type-A (4 pin) USB 2.0
Software	OS Compatibility	OS independent; No software or drivers required
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.4A
	Output Voltage	5 DC
	Output Current	2A
	Center Tip Polarity	Positive
	Plug Type	N
	Plug Type	N
	Plug Type	N
	Power Consumption (In Watts)	10
Environmental	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0%~80%
Physical Characteristics	Color	Black
	Material	Steel
	Product Length	10.0 in [2.5 cm]
	Product Width	1.8 in [45 mm]
	Product Height	4.5 in [1.2 cm]
	Weight of Product	2.3 lb [1.0 kg]
Packaging Information	Package Length	16.3 in [4.2 cm]
	Package Width	8.4 in [2.1 cm]
	Package Height	3.3 in [85 mm]
	Shipping (Package) Weight	3.4 lb [1.5 kg]
What's in the	Included in Package	4 Port DVI KVM Switch

Box

Included in Package	Power Adapter
Included in Package	User Manual
Included in Package	Rubber Feet

****Product appearance and specifications are subject to change without notice.***

