

4 Port DVI USB KVM Switch with Audio & USB Hub

Productcode: SV431DVIUAGB



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs
- Switching USB peripherals between PC's

Eigenschappen

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- Channel selection/Hub port control by front-panel push buttons
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous USB hub port, audio & mic channels and PC port selection
- USB keyboard and mouse support
- HDCP Compliant

Hardware

Garantiebeleid	3 Years
Audio	Ja
KVM-poorten	4
Ondersteunde platforms	USB
PC-videotype	DVI
Multi-monitor	1
Rack-monteerbaar	Optioneel
Inclusief kabels	Nee
Op elkaar aansluitbaar	Nee

Prestaties

Schermmenu & sneltoetsen	Nee
DVI-ondersteuning	Ja
IP-controle	Nee
Hot-Key Selection	Nee
Maximale analoge resoluties	2560x1600 @ 60Hz
Maximale digitale resoluties	1920x1200 @60/70Hz
Maximum aantal gebruikers	1
Poortselectie-ondersteuning	Knopdruk
MTBF	143000 uur

Connector(en)

Console-aansluiting(en)	2 - 3,5 mm mini-jack (3 standen)
	1 - DVI-I (29-polig)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
Hostaansluitingen	8 - 3,5 mm mini-jack (3 standen)
	4 - DVI-I (29-polig)
	4 - USB B (4-polig)
Andere aansluiting(en)	2 - USB 2.0 Type-A (4 pin, 480Mbps)

Software

Besturingssystemen	OS independent; No software or drivers required
--------------------	---

Voeding

Voedingsbron	Inclusief wisselstroomadapter
Ingangsspanning	110V-240V AC
Ingangsstroom	0.4A

Uitgangsspanning	5 DC
Uitgangsstroom	2A
Polariteit pin midden	Positief
Stekkertype	N
	N
Vermogensopname	10

Fysieke eigenschappen

Kleur	Zwart
Type behuizing	Staal
Lengte product	0.0 in [0.0 mm]
Breedte product	10.0 in [25.3 cm]
Hoogte product	1.8 in [4.5 cm]
Diepte product	4.5 in [115 mm]
Gewicht product	2.2 lb [1.0 kg]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	17.3 in [44.0 cm]
Package Width	8.3 in [21.0 cm]
Package Height	3.4 in [8.6 cm]
Verzendgewicht (verpakt)	3.5 lb [1.6 kg]

Wat wordt er meegeleverd

Meegeleverd	1 - 4 Port DVI KVM Switch
	1 - Pack Rubber Feet

1 - Power Adapter

1 - User Manual

Garantiebepalinge
n

Warranty

3 Jaar

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.