

4 Port DVI USB KVM Switch with Audio & USB Hub

Product ID: SV431DVIUAGB



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs
- Switching USB peripherals between PC's

Features

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- Channel selection/Hub port control by front-panel push buttons
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous USB hub port, audio & mic channels and PC port selection
- USB keyboard and mouse support
- HDCP Compliant

Hardware

Warranty	3 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	Optional
Cables Included	No
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	Yes
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	2560x1600 @ 60Hz
Maximum Digital Resolutions	1920x1200 @60/70Hz



Maximum Number of Users	1
Port Selection Support	Push Button
MTBF	143000 hours

Connector(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position) DVI-I (29 pin) USB Type-A (4 pin) USB 2.0
Host Connectors	3.5 mm Mini-Jack (3 Position) DVI-I (29 pin) USB B (4 pin)
Other Interface(s)	USB Type-A (4 pin) USB 2.0

Software


OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N N
Power Consumption (In Watts)	10

Physical Characteristics

Color	Black
-------	-------



Material	Steel
Product Width	10.0 in [25.3 cm]
Product Height	1.8 in [45 mm]
Product Depth	4.5 in [11.5 cm]
Weight of Product	35.3 oz [1000 g]

Packaging Information

Package Length	17.3 in [44 cm]
Package Width	8.3 in [21 cm]
Package Height	3.4 in [86 mm]
Shipping (Package) Weight	3.5 lb [1.6 kg]

What's in the Box

Included in Package	4 Port DVI KVM Switch
	Pack Rubber Feet
	Power Adapter
	User Manual

**Product appearance and specifications are subject to change without notice.*

