

4 Port SuperSpeed USB 3.0 VGA KVM Switch with Audio and Cables

Product ID: SV431U3A



The SV431U3A 4-Port USB 3.0 VGAKVM Switch lets you control 4 VGA, USB 3.0-equipped PCs with a single monitor, keyboard, mouse and audio peripheral set. For added convenience, the included KVM cables provide a ready-to-use KVM solution.

This USB 3.0 KVM Switch offers an integrated 2-port hub that supports USB 3.0 data rates up to 5 Gbps, and is backward compatible with USB 2.0 and 1.1/1.0 devices, ensuring flawless performance for your USB peripherals.

Offering support for high resolutions (up to 2048x1536), this 4-port VGA KVM switch has the ability to drive large VGA displays with ease, making it ideal for graphical applications that require high-res video output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications
- Integrated USB 3.0 hub and Mic/Audio allows the user to have full multimedia control of two computers and share USB peripherals in a home or office
- Control four VGA USB computers with a single set of console peripherals (Keyboard, Mouse and Monitor)

Features

- Integrated USB 3.0 (5 Gbps) hub

- Hot-key and front-panel push buttons for easy computer selection
- Video, audio and USB cables included
- USB keyboard and mouse console connections
- Supports resolutions up to 2048x1536
- No software or drivers required
- Stereo audio and microphone support

Hardware	Warranty	2 Years
	Audio	Yes
	KVM Ports	4
	PC Interface	USB 3.0
	PC Video Type	VGA
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	Yes
	Daisy-Chain	No
Performance	On-Screen Display	No
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Cable Length	32.8 ft [10 m]
	Maximum Analog Resolutions	2048 x 1536
	Audio Specifications	2-Channel Stereo supported
	Port Selection Support	Push Button and Hotkeys
	MTBF	183,411 Hours
Connector(s)	Console Interface(s)	VGA (15 pin, High Density D-Sub)
	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	Host Connectors	VGA (15 pin, High Density D-Sub)
	Host Connectors	USB Type-B (9 pin) USB 3.0
	Host Connectors	3.5 mm Mini-Jack (3 Position)
	Other Interface(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software	OS Compatibility	OS independent; No software or drivers required
Indicators	LED Indicators	PC Selection Indicator
	LED Indicators	Hub selection indicator
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.5 A
	Output Voltage	9V DC
	Output Current	2 A
	Center Tip Polarity	Positive
	Plug Type	M
Environmental	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (4F to 140F)
	Humidity	0~90% RH Non-Condensing
Physical Characteristics	Color	Black
	Material	Steel
	Product Length	10.0 in [2.5 cm]
	Product Width	4.0 in [1.0 cm]
	Product Height	1.8 in [45 mm]
	Weight of Product	33.1 oz [938 g]
Packaging Information	Package Length	10.6 in [2.7 cm]
	Package Width	7.5 in [1.9 cm]
	Package Height	6.3 in [1.6 cm]
	Shipping (Package) Weight	6.9 lb [3.1 kg]
What's in the Box	Included in Package	4 Port USB 3.0 KVM Switch
	Included in Package	VGA M/M Cables
	Included in Package	USB 3.0 A-B Cables
	Included in Package	3.5mm Audio/Mic Cables
	Included in Package	Universal Power Adapter (NA/UK/EU)

Included in Package

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

