

4 Port DVI USB KVM Switch with Audio and USB 2.0 Hub

Product ID: SV431UADVIGB



This 4-Port DVI+USB KVM Switch with Audio and USB 2.0 Hub allows you to control 4 USB-enabled multimedia computers with DVI video interfaces, using only one USB keyboard, mouse, monitor and a set of speakers and microphone.

A cost-effective and versatile KVM solution, the DVI+USB KVM switch features an integrated, 2-port USB 2.0 hub that lets selected computers access shared high speed USB devices, eliminating the cost of duplicate USB peripheral purchases.

The DVI KVM switch supports audio and microphone switching functions and allows you to select connected computers, USB device hub ports and audio/mic channels either simultaneously or independently, using either front-panel push-buttons or keyboard hotkeys.

Ensuring high quality video capability, the DVI KVM switch supports display resolutions of up to 1920 x 1200, and offers genuine digital signal transmission over the cable, reducing the distortion that's common from conventional analog/digital conversion.

Designed for durability and dependability, StarTech.com's 4-Port DVI+USB KVM Switch with Audio and USB 2.0 Hub is backed by StarTech.com's 2-year Warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Sharing computers and USB devices in the home/SOHO/multimedia environment

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Switches instantly between PCs
- Switching USB peripherals between PC's

Features

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- USB keyboard and mouse support
- USB 2.0 Specification compliant
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous USB hub port, audio & mic channels and PC port selection
- Channel selection/Hub port control by front-panel push buttons and keyboard hotkeys
- HDCP Compliant

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

DVI Support	Yes - Single Link
IP Control	No
Hot-Key Selection	Yes

Maximum Digital Resolutions	1920 x 1200 (digital only)
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) 1 - DVI-I (29 pin) 2 - USB 2.0 Type-A (4 pin, 480Mbps)
Host Connectors	8 - 3.5 mm Mini-Jack (3 Position) 4 - DVI-I (29 pin) 4 - USB B (4 pin)
Other Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)

Indicators

LED Indicators	4 - On Line PC 4 - Selected PC
----------------	-----------------------------------

Power

Power Source	AC Adapter Included
Input Voltage	230 AC
Output Voltage	9V DC
Output Current	0.5A
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)

Physical

Characteristics

Color	Black
Material	Aluminum
Product Width	1.8 in [4.5 cm]
Product Height	10.0 in [25.3 cm]
Product Depth	4.5 in [115 mm]
Weight of Product	3.6 lb [1.6 kg]

Packaging Information

Package Length	11.4 in [29 cm]
Package Width	9.8 in [25 cm]
Package Height	3.1 in [80 mm]
Shipping (Package) Weight	3.9 lb [1.8 kg]

What's in the Box

Included in Package	1 - 4 Port DVI KVM Switch
	1 - Power Adapter
	1 - User Manual

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***