

4 Port Rack Mountable USB KVM Switch with Audio & USB 2.0 Hub

Product ID: SV431USBAE



This Rack Mountable USB KVM Switch supports high resolution video applications (up to 1920x1440 pixels supported) and audio switching between connected computers, and provides an integrated USB 2.0 hub that lets the selected computer have access shared high speed USB peripherals.

Providing control of up to four computers from a single USB keyboard and mouse peripheral set, the switch features a sturdy all metal chassis and can be rackmounted in a server rack/cabinet using an optional Rackmount Bracket kit (SV431RACK) - minimizing clutter and saving space.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Control up to four computers, sharing a single keyboard, mouse, monitor and speakers.
- Integrated USB 2.0 hub allows you to share up to three USB peripherals between the four computers.

Features

- Designed for high-resolution applications: up to 1920x1440 pixels supported
- All metal chassis for long-term durability
- Integrated USB 2.0 hub allows you to share up to three high-speed USB devices between computers
- Audio switching with microphone and speaker connectivity

- Auto-scan function automatically selects computer sequentially
- Compatible with all USB supported Operating Systems
- Front panel push button computer selection


Hardware

Warranty	3 Years
U Height	1U
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Optional
Cables Included	No
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	1920x1440
Maximum Number of Users	1
Port Selection Support	Push Button
MTBF	136000 hours

Connector(s)



Console Interface(s)	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)
Host Connectors	VGA (15 pin, High Density D-Sub) USB B (4 pin) 3.5 mm Mini-Jack (3 Position)
Other Interface(s)	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	10

Physical Characteristics

Color	Black
Material	Steel
Product Length	8.7 in [22 cm]
Product Width	5.1 in [13 cm]
Product Height	1.8 in [44.5 mm]
Weight of Product	2.2 lb [1.0 kg]

**Packaging
Information**

Package Length	9.6 in [24.5 cm]
Package Width	16.3 in [41.3 cm]
Package Height	3.5 in [90 mm]
Shipping (Package) Weight	3.3 lb [1.5 kg]

**What's in the
Box**

Included in Package	4 Port USB KVM Switch With Audio
	Pack Rubber Feet
	Power Adapter
	Manual

****Product appearance and specifications are subject to change without notice.***

