

4 Port Steel USB KVM Switch with Audio and USB Hub

Product ID: SV431USBAGB



This 4 port USB KVM switch offers native USB control 4 computers using a single keyboard, mouse and VGA monitor peripheral set.

A versatile addition to any operating environment, the USB KVM switch is suitable for graphics-intensive applications, with support for display resolutions of up to 2048x1536 pixels.

A complete multimedia switching solution, the USB KVM Switch also supports audio switching between connected computers and allows you to "lock on" to the desired audio from one computer even if you're controlling a different computer.

Saving both install space and expense, the USB 4 port KVM switch features an integrated USB 2.0 hub, allowing you to share high-speed USB devices between computers as if the peripheral devices were connected directly to the controlled (slave) computers - a cost-effective solution that eliminates the cost of duplicate peripheral purchases, with no compromise on functionality.

Designed to provide a dependable computer control solution, the USB KVM switch is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Controlling two computers using a single keyboard, mouse and monitor

- Integrated USB 2.0 hub allows you to share USB peripherals between computers

Features

- Designed for high-resolution applications: up to 2048 x 1536 pixels supported
- Hotkey switching for ease-of-use
- Metal chassis for long-term durability
- Integrated USB 2.0 hub allows you to share high-speed USB devices between computers
- Audio and/or USB Hub can be locked to a particular port when switching between computers

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048x1536
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (15 pin, High Density D-Sub)
Host Connectors	4 - 3.5 mm Mini-Jack (3 Position)
	4 - USB B (4 pin)
	4 - VGA (15 pin, High Density D-Sub)
Other Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)

Power

Power Source	AC Adapter Included
Output Voltage	9V DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	M

Physical Characteristics

Color	Black
Material	Steel
Product Width	10.0 in [25.5 cm]
Product Height	1.8 in [4.5 cm]
Product Depth	4.5 in [115 mm]
Weight of Product	4.0 lb [1.8 kg]

Packaging Information

Package Length	11.6 in [29.5 cm]
Package Width	3.1 in [78 mm]
Package Height	10.0 in [25.4 cm]
Shipping (Package)	3.0 lb [1.4 kg]

Weight

What's in the Box

Included in Package	1 - 4 Port KVM Switch
	1 - Power Adapter
	1 - Instruction Manual

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***