

4 Port USB KVM Switch with Ethernet Switch and Audio & USB Hub

Product ID: SV431USBAN



This 4 Port USB KVM Switch integrates a USB 2.0 hub, Ethernet Switch, and audio switching capability into a unique USB multimedia switching solution.

For simple integration into multimedia applications, the switch supports high resolution VGA video interfaces and allows you to toggle between audio sources. The KVM switch also provides a built-in 5 port 10/100 Mbps Ethernet Hub that allows you to easily network and share Internet connectivity among connected computers while reducing the number of outlets and cables needed in the area - helping to preserve valuable work space.

Plus, the USB KVM switch features a built-in USB 2.0 Hub that allows peripheral sharing for printers, scanners, portable hard drives, etc., with support for high speed USB 2.0 data transfer rates of up to 480 Mbps. This USB KVM Switch is cased in a sturdy metal chassis, and offers a compact form factor that helps preserve valuable desk space.

Certifications, Reports and Compatibility

Applications

- Ideal for financial/banking industries, graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are needed
- Great for imaging machines where network connections are limited

Features

- Multi-function USB KVM switch integrates a USB 2.0 hub, Ethernet switch, and audio
- Controls four computers with a single VGA monitor, USB keyboard and mouse

- Built-in USB 2.0 Hub allows peripheral sharing for printers, scanners, portable hard drives, etc., with data transfer rates of up to 480 Mbps.
- Built-in 5 port 10/100 Mbps Ethernet Hub allows you to easily network and share Internet with your computers
- Hot pluggable - add or remove computers without powering down the switch
- Supports Windows 98/SE/ME/2000/XP/Vista, Linux, MacOS, etc.
- Bi-directional switching and flexible interoperability; switch permits independent PC, independent peripheral, and independent audio function, regardless of KVM switch focus
- 2-year Warranty

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048 x 1536
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position)
----------------------	-------------------------------



	USB Type-A (4 pin) USB 2.0
	VGA (15 pin, High Density D-Sub)
Host Connectors	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)
Other Interface(s)	RJ-11
	RJ-45

Special Notes / Requirements

System and Cable Requirements	Console: VGA or SVGAUSB MouseUSB Keyboard
-------------------------------	---

Indicators

LED Indicators	Orange - PC Activity and Select indicator
	Green - Indicates a USB connection to USB HUB
	Green - Ethernet Link and Activity

Power

Power Source	AC Adapter Included
Input Voltage	115V AC
Output Voltage	5.3 DC
Output Current	2.4A
Center Tip Polarity	Positive
Plug Type	B

Environmental

Operating Temperature	0 ~ 50C
Storage Temperature	-20 ~ 60C
Humidity	0 ~ 80% RH

Physical Characteristics

Color	Black
-------	-------



Material	Steel
Cable Length	Four 6ft (1.8m) KVM Cables
Product Width	10.6 in [27 cm]
Product Height	2.2 in [55 mm]
Product Depth	3.3 in [85 mm]
Weight of Product	32.5 oz [920 g]

Packaging Information

Package Length	13.0 in [33 cm]
Package Width	3.9 in [100 mm]
Package Height	8.5 in [21.6 cm]
Shipping (Package) Weight	5.5 lb [2.5 kg]

What's in the Box

Included in Package	4-Port KVM Switch
	USB KVM Cables
	Firmware Upgrade Cable
	Power Adapter
	User Manual

****Product appearance and specifications are subject to change without notice.***

