

4 Port USB VGA IP KVM Switch with Virtual Media

Product ID: SV441DUSBI



The SV441DUSBI 4 Port USB VGA IP KVM Switch with Virtual Media allows for secure local and remote control of up to 4 computers over a LAN or the Internet. Featuring 2 additional USB ports for peripheral sharing (USB storage, CD ROM, etc.), allowing file transfers and disk emulation for remote application and OS installs.

The IP KVM Switch enables BIOS level control and full boot process interaction, and includes several security features (SSH, SSL, RADIUS and a configurable firewall) to keep your network safe.

This IP KVM can interact with virtually any device that uses an RS-232 serial terminal (routers, switches, PDUs, etc.), using the RPORT Module (sold separately). While the 1U rack-mountable metal chassis makes installation into a rack easy with the 1110EXTRACK.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Access your server BIOS from remote locations
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Enables access to existing KVM switches via TCP/IP for single console remote administration
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice and allows remote access

- Remote access for outsourced server / IT hardware management
- Remote access to mission-critical corporate datacenter servers, increasing uptime

Features

- Remote, BIOS level access to all connected systems
- Works with PC, Mac, Linux and Sun Systems
- Supports DHCP or manual IP configuration
- User ID and SSL password secure web console
- Supports 32 user accounts with SSL encrypted session and web communication data
- Integrated Web Server for browser-based configuration and administration
- Disk emulation allows remote application and operating system installations, or transferring files to, or between attached servers
- Each computer can be named via the OSD menu
- Integrated USB hub for peripheral sharing and file transfer of USB 2.0 devices (backwards compatible with USB 1.1 and 1.0 devices)
- Auto Scan Mode automatically switches between computers for easy monitoring
- Optional mounting bracket - Compact 1U height takes up little rack space
- Flash upgradeable
- Hot-pluggable - add or remove PCs without shutting down
- Multiple user accounts restrict unauthorized access to specific features and / or PCs
- Network Setup and Reset button
- No software or drivers required
- Plug and Play compliant
- Supports 16 bit video
- Supports customized SSL certificates

Hardware

Warranty	3 Years
Audio	No



KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Optional
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	Yes
DVI Support	No
IP Control	Yes
Hot-Key Selection	Yes
Maximum Analog Resolutions	1920 x 1440 pixels local console
Maximum Digital Resolutions	1600 x 1200 @ 85Hz
Maximum Number of Users	1 active user plus up to 4 viewing
Port Selection Support	Hotkeys and OSD (On Screen Display)
General Specifications	TLS version supported: 1.0

Note: The SSL certificate provided is for testing and initialization purposes only and provides minimum strength security. We strongly recommend users upgrade the included certificate with individual SSL Certificate.

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	<p>Adding more than 1 optional PCM815SHNA power switch to the Server Remote Control requires a RPORT module.</p> <p>Source code for the unit operating system is available upon request. Please contact us by</p>
------	---



phone, live chat, or email to make your request. </p><p>This offer is valid for three years from the date of purchase and/or for as long as parts or customer support is offered for this product.</p><p>Charges for the reasonable cost of copying and/or conveying may apply.</p>

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.8A
Output Voltage	12V DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	48

Physical Characteristics

Color	Black
Material	Steel
Product Length	7.9 in [20 cm]
Product Width	7.4 in [18.7 cm]
Product Height	0.9 in [22 mm]
Weight of Product	31.8 oz [900 g]

Packaging Information

Package Length	12.0 in [30.4 cm]
Package Width	4.5 in [11.4 cm]
Package Height	10.9 in [27.6 cm]
Shipping (Package) Weight	9.1 lb [4.1 kg]

What's in the Box



Included in Package	universal power adapter (NA/EU/UK/AU)
	4-port USB KVM switch
	KVM cables
	instruction manual

****Product appearance and specifications are subject to change without notice.***

