

USB VGA KVM Console Extender over CAT5 UTP (500 ft) - TAA

Produkt-ID: SV565UTPU



The SV565UTPU USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Monitor computer-controlled equipment in a factory or warehouse

- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

Merkmale

- **REMOTE OPERATION:** Use the VGA over CAT5 extender to control a USB & VGA KVM or PC up to 500ft (150m) away; Supports hotkey commands, auto-switching between host and remote unit or dedicated control
- **COST-EFFECTIVE KVM EXTENSION:** The KVM Extender provides a cost-effective way to convert existing standard KVM units into remote-access hardware, extending the capabilities of your hardware
- **FLEXIBLE CONFIGURATION:** KVM console extender can be used with a single computer or connected to an existing KVM switch; Offers broad support for USB keyboards, mice, and even most combo/wireless configurations
- **EASY INSTALLATION:** Plug and play KVM over Ethernet extender is easy to install using industry-standard UTP network cables and is OS independent, requiring no software or drivers to install
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this CAT5 KVM extender is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen 2 Years

Audio Nein

KVM-Ports 2

PC-Schnittstelle USB

PC-Videotyp VGA

Mehrfach-Monitor 1

Einbaufähig Nein

Leistung

IP-Steuerung Nein

Max. Übertragungsentfernung 150m [492ft]

Unterstützte 1280 x 1024 @ 300ft/ 100m

Auflösungen	1024 x 768 @ maximum cable length
MTBF	126000 Stunden

Steckverbinder

Konsolen-Schnittstelle(n)	2 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
	1 - VGA (15-polig, High Density D-Sub)
Hostanschlüsse	1 - VGA (15-polig, High Density D-Sub)
Andere Schnittstelle(n)	1 - RJ-45

Software

Betriebssystemkompatibilität	OS independent; No software or drivers required
------------------------------	---

Spezielle Hinweise/Anforderungen

Hinweis	Product weights/measurements and connector types indicate a single unit only (either Host or Remote)
---------	--

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.2A
Ausgangsspannung	12V DC
Ausgangsstrom	1.5A
Polarität der Mittelspitze	Positiv
Steckertyp	M
Stromverbrauch	18

Umgebungsbedingungen

Betriebstemperatur	0°C to 40°C (32°F to 104°F)
--------------------	-----------------------------

Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0~80% RH

Physische Eigenschaften

Farbe	Schwarz
Gehäusotyp	Stahl
Produktlänge	3.0 in [7.5 cm]
Produktbreite	6.1 in [15.5 cm]
Produkthöhe	0.8 in [2.0 cm]
Produktgewicht	1.3 lb [0.6 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.7 in [24.7 cm]
Paketbreite	11.9 in [30.2 cm]
Pakethöhe	3.5 in [8.8 cm]
Versandgewicht (Verpackung)	3.1 lb [1.4 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Host-Gerät
	1 - Remote-Gerät
	2 - 6 ft 2-in-1 USB VGA KVM cables
	8 - Gummifüße
	1 - Netzadapter
	1 - Anleitung

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.