

## USB VGA KVM Console Extender over CAT5 UTP (500 ft) - TAA

**Product ID:** SV565UTPU



The SV565UTPU USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location

- Control remote machines and security monitoring systems

## Features

- **REMOTE OPERATION:** Use the VGA over CAT5 extender to control a USB & VGA KVM or PC up to 500ft (150m) away; Supports hotkey commands, auto-switching between host and remote unit or dedicated control
- **COST-EFFECTIVE KVM EXTENSION:** The KVM Extender provides a cost-effective way to convert existing standard KVM units into remote-access hardware, extending the capabilities of your hardware
- **FLEXIBLE CONFIGURATION:** KVM console extender can be used with a single computer or connected to an existing KVM switch; Offers broad support for USB keyboards, mice, and even most combo/wireless configurations
- **EASY INSTALLATION:** Plug and play KVM over Ethernet extender is easy to install using industry-standard UTP network cables and is OS independent, requiring no software or drivers to install
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this CAT5 KVM extender is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No

---

### Performance

IP Control	No
Max Transfer Distance	150m [492ft]
Supported Resolutions	1280 x 1024 @ 300ft/ 100m 1024 x 768 @ maximum cable length
MTBF	126000 hours

---

### Connector(s)

Console Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)
----------------------	-------------------------------------

		1 - VGA (15 pin, High Density D-Sub)
Host Connectors		1 - VGA (15 pin, High Density D-Sub)
Other Interface(s)		1 - RJ-45
<b>Software</b>		
	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>		
	Note	Product weights/measurements and connector types indicate a single unit only (either Host or Remote)
<b>Power</b>		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.2A
	Output Voltage	12V DC
	Output Current	1.5A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	18
<b>Environmental</b>		
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0~80% RH
<b>Physical Characteristics</b>		
	Color	Black
	Material	Steel
	Product Length	3.0 in [7.5 cm]
	Product Width	6.1 in [15.5 cm]

Product Height	0.8 in [2.0 cm]
Weight of Product	1.3 lb [0.6 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	9.7 in [24.7 cm]
Package Width	11.9 in [30.2 cm]
Package Height	3.5 in [8.8 cm]
Shipping (Package) Weight	3.1 lb [1.4 kg]

---

#### What's in the Box

Included in Package	1 - host unit
	1 - remote unit
	2 - 6 ft 2-in-1 USB VGA KVM cables
	8 - rubber feet
	1 - power adapter
	1 - instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***