

## USB VGA KVM Console Extender over CAT5 UTP (500 ft)

**Product ID:** SV565UTPU



The SV565UTPU USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

### Features

- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable

- Intuitive hotkey commands
- Supports auto-switching between host and remote users or dedicated control
- Supports most combo keyboard and mouse sets (including Wireless)
- PS/2 and USB host PC's supported via the appropriate PS2 or USB KVM cable (USB style included)

---

#### Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No

---

#### Performance

IP Control	No
Max Transfer Distance	150 m (492 ft)
Supported Resolutions	1280 x 1024 @ 300ft/ 100m 1024 x 768 @ maximum cable length
MTBF	126000 hours

---

#### Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0
Host Connectors	VGA (15 pin, High Density D-Sub)
Other Interface(s)	RJ-45

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	-------------------------------------------------

---

#### Special Notes /



## Requirements

Note Product weights/measurements and connector types indicate a single unit only (either Host or Remote)

---

### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2A
Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4

---

### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

---

### Physical Characteristics

Color	Black
Material	Steel
Product Length	3.0 in [75 mm]
Product Width	6.1 in [15.5 cm]
Product Height	0.8 in [20 mm]
Weight of Product	21.6 oz [612 g]

---

### Packaging Information

Package Length	9.8 in [24.8 cm]
Package Width	11.6 in [29.4 cm]



Package Height	3.3 in [83 mm]
Shipping (Package) Weight	3.0 lb [1.3 kg]

---

**What's in the Box**

Included in Package	remote unit
	host unit
	power adapter
	instruction manual
	6 ft 2-in-1 USB VGA KVM cables
	rubber feet

---

***\*Product appearance and specifications are subject to change without notice.***

