

USB VGA Console Extender over CAT5 UTP (500 ft)

ID del Producto: SV565UTPUGB



The SV565UTPUGB USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Certificaciones, Reportes y Compatibilidad

Aplicaciones

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

Características

- Can be used with a single computer or connected to an existing KVM switch

- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands
- Supports auto-switching between host and remote users or dedicated control
- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Supports most combo keyboard and mouse sets (including Wireless)
- Cables Included for a ready out of the box setup

Hardware

Política de Garantía	2 Years
Soporte de Audio	No
Cantidad de Puertos KVM	2
Plataformas Admitidas	USB
Tipo de Video PC	VGA
Soporte de Pantalla Doble	1
Montaje en Rack	No

Rendimiento

Control IP KVM	No
Distancia Máxima de Transferencia	150 m (492 ft)
Resoluciones Admitidas	1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)
MTBF	126000 horas

Conector(es)

Interfaz(ces) de Consola	VGA (15 pines, D-Sub de alta densidad)
--------------------------	--



USB Type-A (4 pines) USB 2.0

Conectores del Host VGA (15 pines, D-Sub de alta densidad)

Otra(s) Interfaz(ces) RJ-45

Software

Compatibilidad OS OS independent; No software or drivers required

Observaciones / Requisitos

Nota Product weights, measurements and connectors indicate a single unit only (either Host or Remote)

Requisitos de Energía

Adaptador de Corriente Incluido Adaptador de alimentación de CA incluido

Tensión de Entrada 100 - 240 AC

Corriente de Entrada 0.2 A

Tensión de Salida 9V DC

Alimentación de Salida 0.6 A

Polaridad Central Positivo

Tipo de Enchufe M

Consumo de Energía 5.4

Requisitos Ambientales

Temperatura Operativa 0°C to 40°C (32°F to 104°F)

Temperatura de Almacenamiento -20°C to 60°C (-4°F to 140°F)

Humedad 0~80% RH

Características Físicas

Color Negro



Tipo de Gabinete	Acero
Longitud del Producto	3.0 in [75 mm]
Ancho del Producto	6.1 in [15.5 cm]
Altura del Producto	0.8 in [20 mm]
Peso del Producto	10.6 oz [299 g]

Información de la Caja

Longitud de la Caja	11.8 in [30 cm]
Ancho de la Caja	9.8 in [25 cm]
Altura de la Caja	3.5 in [90 mm]
Peso (de la Caja) del Envío	3.8 lb [1.7 kg]

Contenido de la Caja

Incluido en la Caja	6 ft 2-in-1 USB VGA KVM cables
	Host Unit
	Manual
	Power Adapter
	Remote Unit
	Packs Rubber Feet

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.

