

USB VGA Console Extender over CAT5 UTP (500 ft)

Product ID: SV565UTPUGB



The SV565UTPUGB USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

Features

- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Cables Included for a ready out of the box setup

- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands
- Supports most combo keyboard and mouse sets (including Wireless)
- Supports auto-switching between host and remote users or dedicated control

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No

Performance

IP Control	No
Max Transfer Distance	150 m (492 ft)
Supported Resolutions	1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)
MTBF	126000 hours

Connector(s)

Console Interface(s)	USB Type-A (4 pin) USB 2.0 VGA (15 pin, High Density D-Sub)
Host Connectors	VGA (15 pin, High Density D-Sub)
Other Interface(s)	RJ-45

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---



Special Notes / Requirements

Note	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2 A
Output Voltage	9V DC
Output Current	0.6 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

Physical Characteristics

Color	Black
Material	Steel
Product Length	3.0 in [75 mm]
Product Width	6.1 in [15.5 cm]
Product Height	0.8 in [20 mm]
Weight of Product	10.6 oz [299 g]

Packaging Information

Package Length	11.8 in [30 cm]
----------------	-----------------



Package Width	9.8 in [25 cm]
Package Height	3.5 in [90 mm]
Shipping (Package) Weight	3.8 lb [1.7 kg]

What's in the Box

Included in Package	Host Unit
	Remote Unit
	6 ft 2-in-1 USB VGA KVM cables
	Packs Rubber Feet
	Power Adapter
	Manual

****Product appearance and specifications are subject to change without notice.***

