

## Remote User Station for Enterprise IP KVM Switch

**Product ID:** SV5CONS



This Remote User Station for Enterprise Series IP KVMs provides system administrator access to StarTech.com Enterprise series KVM solutions (i.e. SV1653DXI) located up to 1000 ft. (300m) away - allowing convenient control of two separate KVM solutions without the need of a complete work station.

## Certifications, Reports and Compatibility



## Applications

- Allows a remote user to have local access to the KVM and attached servers.
- Control two enterprise series KVMs from one remote location up to 1000ft. away.

## Features

- Supports a resolution of up to 1280 x 1024 @75, 1000ft. (300m) away
- LED indicator for KVM identification
- Supports most standard USB keyboards and mice
- Hot-key support
- Compact design, with durable hardened metal casing

---

## Hardware

Warranty	2 Years
Audio	No
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No

---

## Performance

IP Control	No
Max Transfer Distance	300m [984ft]
Maximum Analog Resolutions	1280 x 1024 @75Hz

---

## Connector(s)

Console Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (15 pin, High Density D-Sub)
Host Connectors	2 - RJ-45

---

## Indicators

LED Indicators	1 - Green – Port Indicator
----------------	----------------------------

---

## Power

Power Source	AC Adapter Included
Input Voltage	115V AC
Output Voltage	5 DC
Output Current	3A
Center Tip Polarity	Positive

---

## Physical

## Characteristics

Color	Black
Material	Aluminum
Product Length	4.0 in [10.2 cm]
Product Width	4.4 in [11.2 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	6.7 oz [190 g]

## Packaging Information

Package Length	12.6 in [32 cm]
Package Width	2.5 in [63 mm]
Package Height	5.2 in [13.2 cm]
Shipping (Package) Weight	1.5 lb [0.7 kg]

## What's in the Box

Included in Package	1 - Remote User Station
	1 - Power Adapter
	1 - Instruction Sheet

## Warranty Information

Warranty	2 Years
----------	---------

***\*Product appearance and specifications are subject to change without notice.***