

8 Port Rackmount USB VGA KVM Switch w/ Audio (Audio Cables Included) - TAA

Produkt ID: SV831DUSBAU



The SV831DUSBAU 8 Port Rack Mount USB VGA KVM Switch (with Audio Cables Included) allows you to control up to 8 USB computers using a single keyboard, mouse and monitor, and features Audio and Microphone ports to switch between audio signals as well as PC ports.

Based on a 1U rack mountable slim form factor design, this 8 Port USB KVM uses rear cable connections to maximize space efficiency. Multiple KVM units can also be connected (cascaded) together for control of up to 64 computers, ensuring a scalable KVM solution that can be expanded as necessary.

To ensure seamless operation, the switch features automatic and manual scan modes, supports both hot-key and front panel push-button switching, and features a convenient OSD (on-screen display) for added configuration options.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

The SV831DUSBAU only works with specific 2-in-1 VGA and USB cables (sold separately), a list of StarTech.com approved cables are below:

6 ft Ultra Thin USB VGA 2-in-1 KVM Cable

6 ft Ultra Thin USB VGA 2-in-1 KVM Cable

10 ft Ultra Thin USB VGA 2-in-1 KVM Cable

15 ft Ultra Thin USB VGA 2-in-1 KVM Cable

Certifikat, rapporter och kompatibilitet



Användning

- Add single console administration to your Co-location/ISP facility saving you time and money
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Access multiple Security and DVR control systems from one place
- Monitor multiple systems simultaneously in Software QA labs

Funktioner

- Supports Hotkey and front panel push-button switching
- Identify and select computers by names assigned via the OSD menu
- OSD security allows each PC to be password protected
- Supported Wide Screen Resolutions: 1920x1200, 1920x1080, 1680x1050, 1400x1050, 1440x900, 1360x768
- Supported 4:3 Resolutions: 1920x1440, 1600x1200, 1280x1024, 1024x768
- Auto-scan function automatically selects computer sequentially
- Cascade configuration expands system capability
- USB console interface
- Plug-and-play system configuration
- USB Keyboard and Mouse combo supported on one USB connection

Hårdvara

Garantipolicy	3 Years
U-höjd	1U
Audio	Ja
KVM-portar	8
PC-gränssnitt	USB
PC-videotyp	VGA
Flera skärmar	1
Hyllmonterbar	Ja
Medföljande kablar	Nej
Kedjekoppling	Ja

Prestanda

Skärmvisning (OSD) & stöd för snabbtangenter	Ja
IP-kontroll	Nej
Hot-Key Selection	Ja
Maximal analog upplösning	1920 x 1440@60Hz (1920 x 1200@60Hz - Wide Screen)
Stöd för widescreen	Ja
Maximalt antal användare	1
Maximalt antal överlappade datorer	64
Stöd för portval	Tryckknapp, genvägskommandon och OSD (visning på skärmen)
Medeltid mellan fel (MTBF)	150000 hours

Kontakt(er)	Konsolgränssnitt	2 - 3.5 mm minijack (3-polig)
		2 - USB 2.0 Type-A (4 stift, 480 Mbps)
		1 - VGA (15-stifts, High Density D-Sub)
	Värdkontakter	16 - 3.5 mm minijack (3-polig)
		8 - VGA (15-stifts, High Density D-Sub)
Mjukvara	OS-kompatibilitet	OS independent; No software or drivers required
Särskilda anmärkningar/krav	Obs.	Package includes eight 6ft. green audio cables and eight 6ft. red microphone cables. Other lengths and options are available on the accessories page.
Indikatorer	LED-indikatorer	1 - Green - Power
		8 - Green - Online PC
		8 - Red - Selected PC
Ström	Strömförbrukning	48
Miljö	Drifttemperatur	5°C to 40°C (41°F to 104°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	80% RH
Utseende	Färg	Svart
	Kabinetttyp	Stål
	Produktbredd	21.3 in [54 cm]
	Produkthöjd	1.8 in [4.5 cm]

Produktdjup	7.1 in [180 mm]
Produktvikt	5.7 lb [2.6 kg]

Förpackning

Förpackningsantal	1
Paketets längd	10.4 in [26.3 cm]
Paketets bredd	23.5 in [59.8 cm]
Paketets höjd	4.8 in [12.3 cm]
Fraktvikt (förpackning)	10.0 lb [4.5 kg]

Vad det är i lådan

Ingår i paketet	1 - KVM Switch
	2 - Mounting Brackets
	8 - 6ft. Green Audio Cables and Red Microphone Cables (16 in Total)
	4 - Foot Pad
	3 - 6 ft. Power Cords (NA, EU, UK)
	1 - User Manual

Warranty Information

Warranty	3 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.