

DC Power Adapter - 12V, 2A

Product ID: SVA12M2NEUA



This 12V DC power supply can provide a power source for any electronic device that has an M-type barrel and requires 12 volts and up to 2 amps of power.

The power supply is a perfect replacement for the lost or damaged 12-volt 2-amp power adapter you've used to power your existing electronics.

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This 12V 2A DC power supply is a direct replacement for the power adapters included with the following StarTech.com products:

80 m VGA to Cat 5 Monitor Extender Kit
>1 km VDSL2 Extender Kit
>40 km Gigabit Single Mode Fiber Media Converter LC
>550 m Gigabit Single Mode Fiber Media Converter LC
>550 m Gigabit Multi Mode Fiber Media Converter SC
> 2 km Fiber Media Converter Multi Mode SC
>2 km Multi ModeFiber Media Converter ST
>USB 3.0 Hard DriveEnclosure for 3.5in SATA Drives
>USB 3.0 SATA Hard Drive Docking Station for 2.5 in. or 3.5 in. Drives
>USB 3.1 Single-Bay Dock for 2.5 in. or 3.5 in. HDD
>eSATA or USB 3.0 SATA Hard Drive Dock
>External Docking Station for 2.5 in. or 3.5 in. Hard Drives
>HDMI Over CAT5 HDBaseT Extender
>HDMI Over CAT5 Extender
>VGA Over CAT5 Extender
>2-Port Dual DVI USB KVM Switch
>2-Port DVI VGA Dual Monitor KVM Switch
>2-Port Dual DisplayPort USB KVM Switch
>2-Port Dual VGA KVM Switch
>2-Port Quad DVI KVM Switch
>4-Port Dual DVI KVM Switch
>4-Port DVI VGA Dual Monitor KVM Switch
>4-Port DisplayPort KVM Switch
>4-Port Dual VGA KVM Switch

The SVA12M2NEUA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Replace a lost or broken 12V DC power supply
- Keep an extra power adapter on hand for your mission-critical devices

Features

- Supports a range of devices that require 12 volts and 2 amps (or less) of power and a M-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

Connector(s)

Warranty	2 Years
Output Connectors	M-Type Barrel (Inner Diameter: 2.1 mm, Outer Diameter: 5.5 mm)

Power

Power Source	AC Adapter Included
Input Voltage Frequency	50/60Hz
Input Voltage	100 - 240 AC
Input Current	0.6 A
Output Voltage	12V DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	24

Physical Characteristics

Cable Length	4.0 ft [1.2 m]
Product Length	3.0 in [75.0 mm]
Product Width	1.6 in [40.0 mm]
Product Height	1.7 in [43.0 mm]
Weight of Product	4.8 oz [137.0 g]

**Packaging
Information**

Package Length	4.1 in [10.4 cm]
Package Width	3.5 in [89.0 mm]
Package Height	2.4 in [60.0 mm]
Shipping (Package) Weight	7.4 oz [210.0 g]

**What's in the
Box**

Included in Package	universal power adapter (NA, EU, UK, AU)
---------------------	--

****Product appearance and specifications are subject to change without notice.***

