

USB 2.0 S-Video and Composite Video Capture Cable

Product ID: SVID2USB2NS



The SVID2USB2NS USB 2.0 S-Video and Composite video Capture Cable lets you connect devices that output S-Video or Composite video to a computer, through an available USB 2.0 port.

The perfect solution for bridging a computer and an S-Video or Composite video source, the capture cable offers real time MPEG 1, MPEG 2 and MPEG 4 recording. Small enough to fit in the palm of your hand, the Capture Cable is a great solution for mobile applications and integrates seamlessly with laptop and desktop computers.

If you require audio with your video capture please see StarTech.com's S-Video to USB 2.0 Video Capture Cable(SVID2USB2).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert VHS home movies to digital format
- Import recorded videos into your computer system for editing and make your own compilation
- Connect your VCR, camcorder, or any other analog video source to your desktop or notebook PC and capture your video in MPEG 1/2/4 format

Features

- Small and lightweight for portability or on the go applications

- USB 2.0 transfer rates for high quality video capturing
- Choose from MPEG 1 / MPEG 2 / MPEG 4 video encoding
- Up to 30 fps motion capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- SnapShot function allows you to capture still images
- USB powered device - requires no external power adapter
- Supports NTSC, and PAL
- Control brightness, contrast, and sharpness

Hardware

Warranty	2 Years
AV Input	Composite S-Video
AV Output	USB
Audio	No
Industry Standards	Video Input - NTSC, PAL, SECAM File Encoding - MPEG 1, MPEG 2, MPEG 4

Performance

Maximum Data Transfer Rate	480Mbps
Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)
MTBF	100,000 Hours

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	Composite Video (1 x RCA) S-Video (4 pin, Mini-DIN)

Software

OS Compatibility	Windows 8/8.1 (32/64bit), 7 (32/64bit), Vista(32/64), XP(32/64), 2000 Windows Server 2008 R2
------------------	---



Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

Physical Characteristics

Color	Black
Cable Length	34.0 in [86.4 cm]
Product Length	3.5 ft [1.1 m]
Product Width	1.2 in [30 mm]
Product Height	0.5 in [12 mm]
Weight of Product	2.7 oz [76 g]

Packaging Information

Package Length	9.2 in [23.3 cm]
Package Width	2.5 in [64 mm]
Package Height	6.6 in [16.8 cm]
Shipping (Package) Weight	16.9 oz [480 g]

What's in the Box

Included in Package	USB Video Capture Cable
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

