

## KM Switch Cable with File Transfer for Mac and PC - USB 2.0

**Product ID:** SVKMS2



The SVKMS2 2 Port USB Keyboard Mouse Switch Cable w/ File Transfer for PC and Mac enables you to control two computer systems using a single keyboard and mouse set, and offers the ability to transfer files between the connected Windows and/or Mac systems.

Offering automated installation (no additional software or drivers required), this compact KM switch cable connects your Windows and/or Mac systems using a standard USB 2.0 port to make switching between systems as simple as moving the mouse over to your second display, or using hot-keys.

This simple 2 port USB KM switch also provides the added benefit of clipboard sharing so you can copy and paste text from one system to another, or drag and drop files for effortless transfers and data management.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Perfect for office applications where multiple computers need to be controlled by a single user and desk space is limited
- Great for PC repair or tech bench environments, allowing you to control and monitor two systems simultaneously
- A convenient solution for the business user needing to transfer files between their desktop and laptop systems

### Features

- Keyboard and mouse sharing between 2 computers

- Compatible with Windows and Mac systems
- Simple switching between systems via mouse movement, or hot-keys
- Drag and drop file transfer
- Copy and paste text between systems
- Plug-and-Play, no software/driver CD required

---

**Hardware**

Warranty	2 Years
KVM Ports	2
PC Interface	USB
Rack-Mountable	No
Cables Included	Yes
Chipset ID	MCT - WH88
Daisy-Chain	No

---

**Performance**

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Maximum Number of Users	1

---

**Connector(s)**

Host Connectors	USB Type-A (4 pin) USB 2.0
-----------------	----------------------------

---

**Software**

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2012, 2012-R2, 2016, 2019 macOS 10.6 to 10.15
Microsoft WHQL Certified	Yes

---

**Indicators**



LED Indicators                      Power / Link

**Power**

Power Source                      USB-Powered

**Environmental**

Operating Temperature      0C to 50C (32F to 122F)

Storage Temperature        -10C to 55C (14F to 131F)

Humidity                          85% RH (Non-Condensing)

**Physical Characteristics**

Color                                Black

Material                            Plastic

Cable Length                    6.0 ft [1.8 m]

Product Length                6.0 ft [1.8 m]

Product Width                  0.7 in [18.5 mm]

Product Height                0.5 in [11.5 mm]

Weight of Product              1.4 oz [40 g]

**Packaging Information**

Package Length                7.0 in [17.8 cm]

Package Width                 6.3 in [15.9 cm]

Package Height                0.8 in [20 mm]

Shipping (Package) Weight    4.1 oz [116 g]

**What's in the Box**

Included in Package            Keyboard Mouse Sharing Cable

Instruction Manual

*\*Product appearance and specifications are subject to change without notice.*

