

10 ft 3-in-1 Universal PS/2 KVM Cable

Produkt ID: SVPS23N1_10



StarTech.com's universal series PS/2 KVM switch cables prevent tangles and keep your workspace neat while delivering excellent performance with your StarTech.com StarView or other KVM switch.

This 10ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and durable performance. Like all StarTech.com cables, this product comes with a Lifetime warranty.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

Triplite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Certifikat, rapporter och kompatibilitet

Användning

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

Funktioner

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite cores at both ends of video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

Kontakt(er)

Garantipolicy	Lifetime
Connector A	PS/2 (6-stifts, Mini-DIN) VGA (15-stifts, High Density D-Sub)
Connector B	PS/2 (6-stifts, Mini-DIN) VGA (15-stifts, High Density D-Sub)

Utseende

Kabellängd	10.0 ft [3.0 m]
------------	-----------------

Förpackning

Package Length	5.4 in [13.7 cm]
Package Width	0.9 in [24 mm]
Package Height	12.1 in [30.8 cm]
Fraktvikt (förpackning)	20.8 oz [590 g]

Vad det är i lådan

Ingår i paketet	10 FOOT PS/2 STYLE 3 IN 1 KVM SWITCH CABLE DB15 male/male gender changer (GC15HSM) metal part of thumbscrew must be 1.17in(3cm) THUMBSCREWS MUST BE 1.93 inches long (4.9cm) THUMBSCREWS MUST BE 1.93in(4.9cm)
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

