

## 6 ft 3-in-1 PS/2 KVM Cable

**Product ID:** SVPS23N1\_6



The SVPS23N1\_6 6ft 3-in-1 PS/2 KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and reliable connections.

Our universal PS/2 KVM switch cables are designed to prevent tangles and keep your workspace neat, while delivering excellent performance with your StarTech.com or other KVM switch.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS78, CS9134, CS9138, CS138A, CS88A, CS82A, CS84A, CS12, CS14, CS124A, CS114A)

Triplite models (B007-008)

Cables to go models (32569, 22391)

IOGear models (GCS82B, GCS138, GCS78KIT, GCS78, GCS138KITUP, GCS138KIT)

Backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- KVM switch cable to be used with OmniView, StarView, SwitchView and Apex KVM switches. (Note: Some non-StarView models may require gender changing cable adapters.)

## Features

- KVM (Keyboard-Video-Mouse) switch cables allows you to connect your computers to a KVM switch
- High quality video cable uses coaxial and twisted pair wiring to maintain optimal video signals
- Ferrite core on video cable minimizes electromagnetic interference and provides crystal clear video
- Available in AT- and PS/2-styles in various cable lengths

---

### Connector(s)

Warranty	Lifetime
Connector A	PS/2 (6 pin, Mini-DIN) VGA (15 pin, High Density D-Sub)
Connector B	PS/2 (6 pin, Mini-DIN) VGA (15 pin, High Density D-Sub)

---

### Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0 mm]
Product Height	0.0 in [0 mm]
Weight of Product	13.1 oz [369.7 g]

---

### Packaging Information

Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]
Package Height	0.6 in [14 mm]
Shipping (Package) Weight	13.3 oz [376.7 g]

---

### What's in the Box

Included in Package	6 Ft. PS/2 Style 3-in-1 KVM Switch Cable
---------------------	--

DB15 male/male gender changer (GC15HSM)

THUMBSCREWS MUST BE 1.93 inches long (4.9cm)  
THUMBSCREWS MUST BE 1.93in(4.9cm)

metal part of thumbscrew must be 1.17in(3cm)

---

***\*Product appearance and specifications are subject to change without notice.***

