

## KM Switch Cable with File Transfer - USB 3.0

**Product ID:** SVUSB3DSA



The SVUSB3DSA 2-Port USB 3.0 Dual System Swap KVM Switch lets you share video, keyboard/mouse input and transfer files between two Windows systems, all through a standard USB 3.0 connection to each. Once connected, you can move your mouse cursor naturally between systems for seamless KVM control.

This USB KVM switch features display sharing (extended or mirrored mode) from either computer, turning your second laptop, tablet or desktop into a shared display. Integrated touchscreen support means that if one or both of your connected systems has a touchscreen, you can use touch to control the computer being mirrored or extended.

Integrated support for file transfers makes it easy to share files through the USB 3.0 KVM connection. With the click of a button, a file transfer window opens that allows you to either drag-and-drop or copy / paste files to any directory on the opposite computer. The device also supports clipboard sharing, so you can copy and paste text from one system to another.

The USB 3.0 interface provides a 5 Gbps data channel to ensure fast file transfers and smooth video streaming / sharing operations, while offering backward compatibility with USB 2.0.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Share video card and hard disk resources between two computers with display sharing and file transfer support
- Control two systems with a single keyboard and mouse
- Use a Windows touch screen tablet or laptop to control a standard non-touch system

## Features

- Keyboard, mouse and display sharing between 2 Windows systems
- Single USB 3.0 connection per system
- Supports file transfer and clipboard sharing
- Touchscreen control supported

---

### Hardware

Warranty	2 Years
KVM Ports	2
PC Interface	USB 3.2 Gen 1 (5Gbps)
Rack-Mountable	No
Cables Included	Yes
Chipset ID	MCT - WH90

---

### Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	No
Maximum Number of Users	1

---

### Connector(s)

Host Connectors	2 - USB Type-A (9 pin, 5 Gbps)
-----------------	--------------------------------

---

### Software

OS Compatibility	Windows 8 / 8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64)
------------------	-------------------------------------------------------------

---

## Special Notes / Requirements

System and Cable Requirements	Available USB 2.0/3.0 port (USB 3.0 recommended)
	CPU: Intel Core i3 2.8GHz or higher
	RAM: 2GB memory or higher

## Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-10C to 75C (14F to 167F)
Humidity	0~85% RH (Non-condensing)

## Physical Characteristics

Color	Black
Material	Plastic
Cable Length	4.9 ft [1.5 m]
Product Length	1.9 in [49.0 mm]
Product Width	0.7 in [1.9 cm]
Product Height	0.4 in [0.9 cm]
Weight of Product	1.3 oz [37.0 g]

## Packaging Information

Package Quantity	1
Package Length	6.9 in [17.5 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	5.7 oz [161.0 g]

## What's in the Box

Included in Package	1 - USB 3.0 KM switch cable
	1 - Driver CD

1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***