

3m White Thunderbolt Cable - M/M

Produkt ID: TBOLTMM3MW



This 3m (9.8ft) White Thunderbolt™ cable offers a dependable, high-quality solution for harnessing the speed and power of Thunderbolt technology while combining both data and video into a single high-performance cable.

The TBOLTMM3MW supports both Thunderbolt 1 (10Gbps) and Thunderbolt 2 (20Gbps) devices and can link compatible devices as part of a daisy-chained connection. Plus, with bi-directional data transfer capability and support for power delivery (for bus-powered devices), this Thunderbolt cable offers the performance needed for optimal connections.

This high quality cable is specifically designed to provide a reliable solution for device connections of up to 3m/9.8ft, providing enough cable length to position compatible devices as needed.

Backed by our 2-year Manufacturer's Warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Connect a Thunderbolt-equipped external drive enclosure or RAID array
- Connect two Thunderbolt-equipped Mac® computers, for Target Disk Mode file transfers
- Connect a Thunderbolt-equipped MacBook Pro® to an iMac®, to use the iMac as the display for the MacBook Pro

Funktioner

- Compatible with Thunderbolt 1 and Thunderbolt 2 specifications
- Supports Power-over-cable, for bus-powered Thunderbolt devices
- Supports native peer-to-peer file sharing when supported by the OS

Hårdvara

| | |
|------------------|----------------------------------|
| Garantipolicy | 2 Years |
| Kontaktplätering | Nickel |
| Kabelmanteltyp | PVC - Polyvinyl Chloride |
| Kabelskärmning | Aluminiummylarfolie med flätning |

Prestanda

| | |
|-------------------|---------------------------|
| Typ och hastighet | Thunderbolt 2 - 20 Gbit/s |
|-------------------|---------------------------|

Kontakt(er)

| | |
|-------------|--------------------------|
| Connector A | Thunderbolt™ (20-stifts) |
| Connector B | Thunderbolt™ (20-stifts) |

Ström

| | |
|----------------|-----|
| Power Delivery | 10W |
|----------------|-----|

Utseende

| | |
|---------------|------------------|
| Färg | Vit |
| Tråddimension | 34 AWG |
| Kabellängd | 9.8 ft [3 m] |
| Produktlängd | 9.8 ft [3.0 m] |
| Produktbredd | 0.4 in [11.0 mm] |
| Produkt höjd | 0.3 in [8.0 mm] |
| Produktvikt | 3.9 oz [110.0 g] |

Förpackning



| | |
|-------------------------|------------------|
| Förpackningsantal | 1 |
| Package Length | 8.9 in [22.5 cm] |
| Package Width | 4.9 in [12.5 cm] |
| Package Height | 0.7 in [18.0 mm] |
| Fraktvikt (förpackning) | 4.2 oz [120.0 g] |

Vad det är i lådan

| | |
|-----------------|----------------------------------|
| Ingår i paketet | 3m White Thunderbolt Cable - M/M |
|-----------------|----------------------------------|

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

