

2.5in Tool-less USB 2.0 to IDE SATA External Hard Drive Enclosure

Produkt ID: UNI2510U2V



The UNI2510U2V 2.5" HDD Enclosure offers versatile data storage, letting you turn a 2.5" SATA or IDE hard drive (HDD) or solid state drive (SSD) into an external hard drive connected through USB 2.0 - a cost-effective solution for a variety of uses including data backups, digital image storage, multimedia storage, or simply putting an "outdated" legacy hard drive (IDE) to good use. Large capacity drives (tested with up to 1TB) can be used to greatly enhance your computer's storage/backup capabilities. The external hard drive enclosure features a tool-less design that eliminates the time (and tools) that would typically be required to install or replace a hard drive in an external enclosure. The USB-based enclosure also offers the "One Touch Backup" feature, which lets you automate backups that can be triggered at the touch of a button, instead of having to manually drag and drop folders and files from the host computer to the external HDD. The UNIV2510U2V USB IDE/SATA hard drive enclosure includes a USB Y-cable that when (both USB connectors) are connected to the powered host computer eliminates the need for an external power adapter for the external drive.

Certifikat, rapporter och kompatibilitet

Användning

- Turn an unused IDE (PATA) or SATA hard drive into additional external storage
- Technicians who work with and need to access a variety of different drives
- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on storage to almost any USB enabled system
- Backup data to an external storage device for archiving or freeing up space

Funktioner

- Supports either SATA or IDE (PATA) drives
- Screwless/tool-less design for assembly
- Power/Activity LED indicator
- Powered directly from the USB port(s)
- Support for One-Touch backup software
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) and IDE 66/100 Mbps drives
- Supports 2.5" form factor hard drives (HDD) and solid state drives (SSD) up to 9.5mm in height
- Plug-and-Play and compatible

Hårdvara

Garantipolicy	2 Years
Fläkt(ar)	Nej
Gränssnitt	USB 2.0
Antal enheter	1
Enhetsstorlek	2.5in
Enhetsstyp	SATA & IDE
Enhetsinstallation	Fixerad
Chipset-ID	JMicron - JM20337

Prestanda

Typ och hastighet	USB 2.0 - 480 Mbit/s
UASP-stöd	Nej
RAID	Nej
Maximal	Currently tested with up to 1TB 5400 RPM hard drives



enhetskapacitet

Kontakt(er)

Enhetskontakter	IDE (44-stifts, EIDE/PATA, 2,5" HDD) SATA data- & ström-kombo (7+15-stifts)
Värdkontakter	USB Mini-B (5-stifts)

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

Indikatorer

LED-indikatorer	Blue (Solid - Power, Blinking - Activity)
-----------------	---

Miljö

Drifttemperatur	0°C to 60°C (32°F to 140°F)
Förvaringstemperatur	-20°C to 70°C (-4°F to 158°F)
Luftfuktighet	0~90% RH

Utseende

Färg	Svart & silver
Kabinettyp	Aluminium och plast
Produktlängd	5.2 in [13.3 cm]
Produktbredd	3.1 in [78 mm]
Produkthöjd	0.7 in [19 mm]
Produktvikt	4.6 oz [130 g]

Förpackning

Package Length	6.8 in [17.3 cm]
Package Width	1.7 in [42 mm]
Package Height	5.2 in [13.3 cm]
Fraktvikt (förpackning)	8.8 oz [250 g]

Vad det är i lådan



Ingår i paketet	2.5in HDD Enclosure
	USB mini-B Y cable
	Driver CD
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

