

2U Vented Sliding Server Rack Shelf w/ Cable Management Arm - 27.6 to 31.6in Adjustable Mounting Depth - 110lb - 19" Server Tray Shelf for Equipment Rack - 24in Deep - TAA

**Product ID:** UNISLDSHF19M



The UNISLDSHF19M Adjustable Sliding Rack Shelf lets you add a vented, sliding shelf with cable management into virtually any 4-post server rack or cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The adjustable mounting depth design allows the shelf to be installed easily into server cabinets with mounting depths from 27.7in (702.2mm) to 31.6in (802.2mm). The sliding rails also offer a locking mechanism to stop the shelf from sliding out too far, or sliding back into the rack before maintenance is complete.

Offering a weight capacity of up to 110 lbs (50 kg), this sliding rack shelf features a ventilated, cold-rolled steel construction for increased airflow and durability in your server room or wiring closet installations.

For ease in routing cables neatly through your rack, we've included a reversible cable management arm that can be attached to the back of the shelf, plus an adjustable bezel to keep your equipment where you want it on the shelf.

## Certifications, Reports and Compatibility



## Applications

- Supply additional storage space for hardware or non-rackmount equipment and peripherals
- Install into virtually any standard 4-post rack or cabinet

## Features

- **UNIVERSAL 19"FIT:** Add a sliding shelf to any 4-post server rack or cabinet for easy peripheral and equipment access; This 19in rack mount tray has a locking feature, preventing the shelf from falling out
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with cold rolled steel, the sturdy IT-grade pull out server rack shelf ensures long term durability and supports a total weight load of 110lb (50kg)
- **CABLE MANAGEMENT:** This sliding cabinet shelf includes integrated cable management & is vented to ensure proper airflow; Ideal for adding additional sliding storage space for your IT / AV accessories
- **COMPACT DESIGN:** The 2U server rack shelf features a compact form factor, making it ideal for non-rackmount equipment, tools and peripherals in your home, studio or office space
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
U Height	2U
Cable Management	Yes
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front and Rear)

---

### Performance

Weight Capacity (Stationary)	125.0 lb [56.7 kg]
------------------------------	--------------------

---

### Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.1 in [2 mm]
Product Length	24.0 in [61.0 cm]
Product Width	19.0 in [48.3 cm]
Product Height	3.5 in [8.9 cm]
Weight of Product	18.0 lb [8.2 kg]
Maximum Mounting Depth	31.6 in [80.2 cm]

Minimum Mounting Depth 27.6 in [70.2 cm]

---

**Packaging Information**

Package Quantity	1
Package Length	29.3 in [74.3 cm]
Package Width	21.7 in [55.1 cm]
Package Height	4.6 in [11.6 cm]
Shipping (Package) Weight	22.2 lb [10.1 kg]

---

**What's in the Box**

Included in Package	1 - Shelf Assembly
	2 - Sliding Rail Assembly
	3 - Locking Bracket
	1 - Rear Stop
	1 - Cable Management Assembly
	1 - Cable Management Locking Bracket
	2 - M5 x 8mm Screws
	2 - M5 Nuts
	2 - M4 x 8mm Screws
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***