

USB 3.0 to Fiber Optic Converter - Compact USB to Open SFP Adapter - USB to Gigabit Network Adapter - USB 3.0 Fiber Adapter Multi Mode(MMF)/Single Mode Fiber(SMF) Compatible

Product ID: US1GA30SFP

This USB 3.0 to fiber-optic converter lets you utilize the USB 3.0 (Type-A) port on your laptop or tablet to provide a secure fiber network connection. Windows and Mac compatible, the network adapter provides a Gigabit Ethernet (1000Mbps) optical network connection for portable laptops or tablets, or systems without expansion slots.

The open SFP slot enables you to use your preferred SFP transceiver module to meet your networking needs - use an SFP with your desired wavelength, distance, and connection type to achieve an efficient network solution. (SFP sold separately.)

This USB to fiber-optic converter provides reliable fiber connectivity while protecting your network from problems with electronic interference - a common issue with copper Ethernet networks. Fiber-to-the-desk connectivity (FTTD) maximizes network security, reducing the risk of data leaks for sensitive information, without compromising network speed and reliability.

Compact and portable, this USB 3.0 to fiber-optic converter is powered directly from the USB port.

Get up and running quickly. The USB to fiber-optic converter supports certified drivers for Windows, Mac and Linux. Once the adapter is plugged into a USB port, you simply install the drivers and the adapter is ready to transmit over a fiber network.

The US1GA30SFP is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Provides a portable network connectivity solution for mobile professionals, to access a fiber network through the USB port on their laptop or tablet
- Ideal for secure network connectivity - a direct fiber connection means no electronic interference, which can be a problem with RJ45 network cards

Features

- **TECH SPECS:** Gigabit 1000Mbps 1x Open SFP (MSA compliant) Realtek RTL8153-VB-CG 1x USB 3.0 Type A Multi-mode (MMF) & Single mode (SMF) Fiber Comp. 9K Jumbo Frames VLAN USB Bus Powered
- **MAXIMUM PORTABILITY:** Compact, lightweight, and cableless design make this USB NIC / Gigabit Network Adapter easy to securely connect your Laptop to a Gigabit Ethernet Network wherever you go
- **FLEXIBLE OPEN SFP SLOT:** Use any MSA compliant SFP+ module; beneficial for network admins, installation technicians, and those who require seamless access to different types of fiber connectivity

- THE STARTECH.COM ADVANTAGE: StarTech.com offers a 2-year warranty on this USB-C to Gigabit Ethernet Adapter and free lifetime 24/5 multilingual technical support based in North America
- 1GbE USB 3.0 TO FIBER OPTIC CONVERTER: For USB-A enabled computers who require occasional access to a fiber LAN, for laptop users who don't have the option of an internal fiber network card

Hardware	Warranty	2 Years
	Ports	1
	Interface	Fiber Ethernet
	Bus Type	USB 3.0
	Industry Standards	IEEE802.3z 1000BASE-SX/LX
	Chipset ID	IEEE 802.1Q VLAN tagging
		Realtek - RTL8153-VB-CG
		Microsemi - VSC8211XVW
Performance	Maximum Data Transfer Rate	1000 Mbps
	Compatible Networks	1000 Mbps (1 Gbps)
	Full Duplex Support	Yes
	Jumbo Frame Support	9K max.
	Promiscuous Mode	Yes
Connector(s)	Connector Type(s)	9 pin USB 3.0 A
	External Ports	SFP Slot
Software	OS Compatibility	Windows 7, 8, 8.1, 10
		Windows Server 2008, 2012, 2016, 2019
		macOS 10.9 - 10.14
		Linux kernel 3.5 to 4.11.x, LTS versions only
Special Notes / Requirements	System and Cable Requirements	USB-enabled computer with an available USB 3.0 port
	System and Cable Requirements	1Gb SFP transceiver with your desired network connection
	Note	Fiber data transfer speeds and distances are dependent on the SFP used (sold separately)
Indicators	LED Indicators	Power

	LED Indicators	Link/Activity
Power	Power Source	USB-Powered
Environmental	Operating Temperature	0C ~ 60C (32 ~ 140F)
	Storage Temperature	-10 ~ 70C (14 ~ 158F)
	Humidity	5% ~ 90% RH
Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	7.7 in [2.0 cm]
	Product Length	6.7 in [1.7 cm]
	Product Width	5.6 in [1.4 cm]
	Product Height	0.8 in [20.000 mm]
	Weight of Product	3.7 oz [106.000 g]
Packaging Information	Package Length	10.4 in [2.6 cm]
	Package Width	6.7 in [1.7 cm]
	Package Height	1.2 in [30.000 mm]
	Shipping (Package) Weight	1.8 oz [52.000 g]
What's in the Box	Included in Package	network adapter
	Included in Package	quick-start guide

**Product appearance and specifications are subject to change without notice.*

