

1-ports USB 2.0 Ethernetförlängare - Upp till 100m förlängning över Cat5/Cat6 -
industriell USB över UTP-repeater

Produkt ID: USB2001EXT2



The USB2001EXT2 USB over Cat5/Cat6 Extender lets you extend a USB 2.0 connection over distances of up to 100-meters (330-feet), over standard Cat5 or Cat6 ethernet cabling.

Backward compatible with USB 1.x devices, the extender enables almost any kind of USB device to be placed at remote locations away from the host computer system.

With data bandwidth of up to 480 Mbps and no software installation required, the USB extender offers a fast, easy, and versatile solution for business or industrial applications with durable metal housing, an included surface-mounting bracket kit, and simple plug-and-play installation.

Plus, the extender provides up to the full 500 mA of power (with the use of an external power adapter at the remote end) allowing for greater compatibility with bus-powered USB devices.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Secured environments where the host computer must be in a secure, inaccessible location from the the keyboard, mouse, camera or other USB input devices
- Industrial control environments where the host computer must be located away from interference or contamination

- Can be used with existing in-wall Cat5/Cat6 ethernet wiring, for extending USB connections between rooms
- Reduce cable clutter and the need for mid-point USB hubs/repeaters by running a single, easy-to-install Cat5/Cat6 cable

Funktioner

- One USB 2.0 port over a single Cat5/Cat6 cable
- Maximum extension distance of up to 100m (330ft) over Cat5 or Cat6 cabling
- Rugged, metal enclosure with surface-mounting bracket kit included
- Hi-Speed USB 2.0 compliant, with support for data transfer rates up to 480 Mbps
- Up to 500mA of power per port, for USB bus-powered devices
- 8kV Contact and 16kV Air Electrical Static Discharge (ESD) protection
- No driver or software installation required

Prominence

Garantipolicy	2 Years
Description CDW 75 - 1st Line	StarTech.com USB Cat5/Cat6 Extender: Newer Version Available USB2001EXT2NA

Hårdvara


Portar	1
Kablage	Cat 5e UTP eller bättre

Prestanda

Maximal dataöverföringshastighet	480 Mbps
Maximalt avstånd	100 m / 330 ft
Frekvensområde	175,316 Hours

Kontakt(er)

Lokala enhetskontakter	USB B (4-stifts)
------------------------	------------------



RJ-45

Fjärrrenhetskontakter USB Type-A (4-stifts) USB 2.0

RJ-45

Mjukvara

OS-kompatibilitet OS Independent; No additional drivers or software required

Särskilda
anmärkningar/
krav

System- och
kabelkrav USB enabled computer system with available USB port

Indikatorer

LED-indikatorer Host Connection
Activity
USB Link
Power
Link

Ström

Power Source AC-adapter medföljer
Inspänning 100 - 240 AC
Inström 0.6A
Utspänning 5 DC
Utström 3A
Kontakttyp C
Strömförbrukning 18

Miljö

Drifttemperatur 0°C to 50°C (32°F to 122°F)
Förvaringstemperatur -20°C to 70°C (-4°F to 158°F)



Luftfuktighet 20~90% RH

Utseende

Färg	Svart
Kabinetttyp	Aluminium
Produktlängd	3.9 in [100.0 mm]
Produktbredd	3.0 in [76.0 mm]
Produkt höjd	1.0 in [26.0 mm]
Produktvikt	11.1 oz [315.0 g]

Förpackning

Förpackningsantal	1
Package Length	7.9 in [20.0 cm]
Package Width	9.8 in [25.0 cm]
Package Height	3.0 in [75.0 mm]
Fraktvikt (förpackning)	2.6 lb [1.2 kg]

Vad det är i lådan

Ingår i paketet	<p>USB 2.0 local extender unit</p> <p>USB 2.0 remote extender unit</p> <p>6 ft [1.8 m] USB cable</p> <p>mounting kit</p> <p>universal power adapter (NA, JP, EU, UK, ANZ)</p> <p>quick-start guide</p>
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

