

## Compact Black USB 2.0 to 10/100 Mbps Ethernet Network Adapter

**Product ID:** USB2106S



This compact USB 2.0 to 10/100 Mbps Ethernet USB Network Adapter offers convenient Ethernet connectivity - simply connect the network adapter to an available USB 2.0 port on your laptop computer, then connect the adapter to the Ethernet network.

Providing full/half duplex operation on both 10Mbps or 100Mbps Ethernet connections, this USB 2.0 Ethernet adapter supports data transfer rates of up to 200Mbps, providing a fully integrated, cost-effective and reliable solution to notebook users requiring Ethernet connectivity.

### **Certifications, Reports and Compatibility**

#### **Applications**

- Replace a failed Ethernet port in a small form factor or laptop/netbook computer
- Add networking capabilities to an old system with no Ethernet port

#### **Features**

- A single 10/100 Mbps compatible RJ45 Ethernet port
- Network Link/Activity and 10/100 Mbps LED indicators
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3x
- Full and half duplex support
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps

- Powered directly from the USB port

---

### Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com Compact USB 2.0 to Ethernet Adapter - 10/100 Mbps Fast Network

---

### Hardware

Ports	1
Interface	RJ45 (10/100 Ethernet)
Bus Type	USB 2.0
Chipset ID	ASIX - MCS7830

---

### Performance

Maximum Data Transfer Rate	100 Mbps (Half Duplex) / 200 Mbps (Full Duplex)
Compatible Networks	10/100 Mbps
Full Duplex Support	Yes

---

### Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0 RJ-45
-------------------	-------------------------------------

---

### Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.5 to 10.14 Linux 2.6.x to 4.11.x <i>LTS Versions only</i> Chrome OS
------------------	---

---

### Indicators

LED Indicators	Speed and Link
----------------	----------------

---

### Environmental

Operating Temperature	0C to 60C (32F to 140F)
-----------------------	-------------------------



Storage Temperature	0C to 60C (32F to 140F)
Humidity	5% ~ 95% RH

---

**Physical Characteristics**

Color	Black
Form Factor	Dongle
Material	Plastic
Product Length	2.7 in [67.5 mm]
Product Width	1.0 in [26.0 mm]
Product Height	0.9 in [22.5 mm]
Weight of Product	0.7 oz [21.0 g]

---

**Packaging Information**

Package Length	6.9 in [17.5 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.3 in [32.0 mm]
Shipping (Package) Weight	3.1 oz [89.0 g]

---

**What's in the Box**

Included in Package	USB Ethernet Adapter
	Driver CD
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

