

2m USB 2.0 A to A Cable - M/M

Produkt ID: USB2AA2M



The USB2AA2M 2-meter USB 2.0 cable features two USB 'A' male connectors, delivering a dependable way to connect your PC to a USB hub, or connect USB 2.0 peripherals to a USB hub.

Fully rated to USB 2.0 performance specifications, this high quality USB cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Connecting USB 2.0 devices to a USB hub
- Connecting USB 2.0 devices directly to a computer
- Replace worn-out or misplaced USB cables with this high quality, 2m USB 2.0 A to A, M/M Cable

Funktioner

- Supports USB 2.0 data transfer rates up to 480 Mbps
- Backward compatible with USB 1.1

- High quality USB 'A' male connectors

Hårdvara

Garantipolicy	Lifetime
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Connector B	1 - USB 2.0 Type-A (4 stift, 480 Mbps)

Miljö

Drifttemperatur	0°C to 50°C (32°F to 122°F)
Förvaringstemperatur	-20°C to 70°C (-4°F to 158°F)
Luftfuktighet	0~95 % RH

Utseende

Färg	Svart
Tråddimension	24/28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	0.5 in [1.2 cm]
Produkthöjd	0.3 in [0.8 cm]
Produktvikt	2.7 oz [76.5 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.8 in [17.2 cm]
Paketets bredd	4.9 in [12.5 cm]
Paketets höjd	0.9 in [2.2 cm]

Fraktvikt (förpackning) 2.8 oz [78.0 g]

Vad det är i lådan

Ingår i paketet

1 - 2 m USB 2.0 A to A Cable - M/M

Warranty
Information

Warranty

Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.