

## 10m USB 2.0 Active Extension Cable - M/F - TAA

**Product ID:** USB2AAEXT10M



The USB2AAEXT10M 10m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 10-meters (30-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables.

Up to 4 of these cables can be daisy-chained together, allowing for a total USB extension of up to 40-meters. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT10M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain up to 4 cables together for even longer USB extensions

### Features

- 1x USB-A male connector
- 1x USB-A female connector
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

---

**Hardware**

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

---

**Special Notes / Requirements**

Note	Cascade up to 4 USB2AAEXT10M devices together for further extension
------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	H

Power Consumption (In Watts) 5

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Cable Length	32.8 ft [10 m]
Product Length	32.8 ft [10.0 m]
Product Width	0.6 in [1.6 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	14.5 oz [410.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	9.0 in [22.8 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.4 in [6.0 cm]
Shipping (Package) Weight	1.5 lb [0.7 kg]

---

**What's in the Box**

Included in Package	1 - 10m USB 2.0 Active Extension Cable - M/F
	1 - Universal Power Adapter
	1 - Plug Adapters for North America, UK, Europe, and Australia

---

***\*Product appearance and specifications are subject to change without notice.***