

10ft (3m) USB-A to USB-C Charging Cable, Charge & Sync, 3A, USB 2.0, TPE Jacket - White USB Charging Cord

Produkt-ID: USB2AC10FWHE



Charge a USB Type-C mobile device or transfer files to a USB-A host computer with this high-quality USB-A to Type-C cable. The USB-A to USB-C charger cord supports up to 15W and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent or daily use, the USB-A to USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

The 10ft (3m) USB Charging Cable is the ideal length for larger desk workstations or for use in locations where extra length is desired.

Facilitating up to 3A of output, the USB-C Charger Cord can fast-charge a smartphone or tablet. To use, connect the cable from a USB-C device to a USB-A wall charger.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **USB-A TO USB-C CHARGING:** High quality USB-A to Type-C cable delivers 3A output for fast charging portable USB-C devices; Connect this cable to a USB-A wall charger, power bank, or charge/access your phone/tablet from a USB-A host
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for fast charging phones and other small peripherals; Supports USB 2.0 (480Mbps) for general use, including file transfer and device synchronization when connected to a USB-A host computer or external storage
- **PERFORMANCE:** Supports 15W/3A Fast Charge; USB 2.0 (480Mbps); Length: 10-foot (3-meter); Color: White; O.D.: 0.16in (4mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **COMPATIBILITY:** Compatible with a wide range of USB-C devices including iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Google Pixel, USB-C portable monitors Asus ZenScreen/ProArt, iPad Pro, MacBook Air/Pro, Surface Book, and more

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	TPE - Thermoplastic Elastomers
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

MTBF	Rated over 10,000 insertion cycles
------	------------------------------------

Steckverbinder

Steckverbinder A	1 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
Steckverbinder B	1 - USB 2.0 Type-C

Spezielle Hinweise/Anforderungen

Hinweis	Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)
---------	--

Strom	Power Delivery	15W
	Eingangsstrom	3A
Umgebungsbedingungen		
	Betriebstemperatur	-10 to 60 (14°F to 140°F)
	Lagertemperatur	-20 to 70 (-4°F to 158°F)
	Feuchtigkeit	5%~85%
Physische Eigenschaften		
	Farbe	Weiß
	Steckverbinderart	Gerade
	Drahtstärke	23/28 AWG
	Gehäusetyp	Polyamide Resin
	Kabellänge	10.0 ft [3.0 m]
	Außendurchmesser des Kabels	0.2 in [4 mm]
	Produktlänge	10.0 ft [3.0 m]
	Produktbreite	0.6 in [1.6 cm]
	Produkthöhe	0.3 in [7.8 mm]
	Produktgewicht	3.4 oz [95.0 g]
Verpackungsinformationen		
	Paketlänge	5.0 in [12.8 cm]
	Paketbreite	8.7 in [22.0 cm]
	Pakethöhe	0.8 in [2.0 cm]
	Versandgewicht (Verpackung)	3.5 oz [100.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - USB-A to USB-C Cable - M/M
--------------------	--------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.