5-Pack 3ft (91cm) USB-A to USB-C Fast Charging Cable, 15W 3A, Dual-Layer Braided Nylon/TPE Jacket, Durable USB-A to Type C Charger Cord, USB A to USB C Cable

Product ID: USB2AC3FBR5PK



Charge a USB Type-C mobile device or transfer files to a USB-A host computer with this high-quality USB-A to Type-C cable. The USB-A to USB-C charger cord supports up to 15W and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use. Quick ID connectors with performance markings eliminate confusion, helping you identify the right cable instantly.

The USB-C Charging Cable features a TPE inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 10,000 insertion cycles.

This durable USB-A to USB-C charging cord is Ideal for workstations in high-density setups or demanding environments. Facilitating up to 15W and 3A of output, the USB-C Charger Cord can fast-charge a smartphone or small tablet. To use, connect the cable from a USB-C device to a USB-A wall charger or hub.

Certifications, Reports and Compatibility

Applications

• Connect and sync a USB-C smartphone or small peripheral device from an available USB-A port on a laptop or desktop computer

• Charge a smartphone or small tablet using a USB-A hub, wall charger, or power bank

• Dual layer jacket combines a flexible TPE inner layer with a braided nylon exterior for optimal durability in

demanding environments

Features

• Fast-Charge Mobile USB-C Devices Anywhere: Charge USB-C smartphones and peripherals with up to 15W / 3A of power from commonly available USB-A ports; This practical 5-pack streamlines deployments and keeps spare charging cables on hand

• Built for Everyday Use: Dual-layer jacket combines a TPE inner layer for flexibility with braided nylon exterior for enhanced durability; Designed to withstand frequent 60 bends, with nickel-plated connectors rated beyond 10,000 insertions

• Identify Specs Instantly: Performance markings printed on each Quick ID connector remove guesswork and confirm feature support at-a-glance; Reduce cable confusion and simplify device deployment in dense workstation or charging environments

• Bridge USB-A and USB-C Devices: Connect USB-C devices to existing USB-A wall chargers, charging stations, hubs, and workstation setups while avoiding unnecessary replacement; Supports USB 480Mbps for general file transfer or sync

• The IT Pro's Choice: Our USB cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030927802
	Package Quantity	5
	Warranty	Lifetime
Power		
	Power Delivery	15W
	Input Current	3A
Physical & Environmental		
	Color	Black
	Connector Style	Straight
	Wire Gauge	21/28 AWG
	Cable Length	36.0 in [91.4 cm]
	Cable OD	0.2 in [4.5 mm]

	Product Length	36.8 in [93.4 cm]
	Product Width	0.6 in [15 mm]
	Product Height	0.3 in [7 mm]
	Weight of Product	1.1 oz [30 g]
	Operating Temperature	-20 to 40 (-4&degF to 104&degF)
	Storage Temperature	-20 to 70 (-4&degF to 158&degF)
	Humidity	30%~70%
Performance		
	Insertion Rating	Rated beyond 10,000 insertions
	MTBF	Rated beyond 10,000 insertions
Hardware		
	Connector Plating	Nickel
	Cable Jacket Material	TPE (Thermoplastic Elastomer) with Braided Nylon
Packaging & In-the-Box		
	Included in Package	5 - Braided USB-A to C Cable
	Package Width	5.1 in [13 cm]
	Package Depth	5.5 in [14 cm]
	Package Height	2.2 in [55 mm]
	Shipping (Package) Weight	7.4 oz [210 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-A (480Mbps, 2.5W)
	Connector 2 (Quantity)	1
	Connector 2	USB-C (480Mbps, 2.5W)

Product appearance and specifications are subject to change without notice.