

10er-Pack 1,8m USB-A zu USB-C-Ladekabel, Laden und Synchronisieren, 3A, USB 2.0, TPE-Mantel, Schwarz - USB Ladekabel

Produkt-ID: USB2AC6FBKE10PK



This 10-Pack of USB-A to USB-C cables is a convenient solution for supporting multiple installations. Charge a USB Type-C mobile device or transfer files to a USB-A host computer. The USB-A to USB-C charger cord supports up to 15W and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent or daily use, the USB-A to USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

The 6ft (1.8m) USB Charging Cable is the ideal length for desk workstations or for use in locations where extra length is desired.

Charge a USB-C device with a USB-A wall charger, car charger, or power bank. It is a convenient length for commuters working from mobile setups or to reduce clutter when syncing with a USB-A laptop.

Facilitating up to 3A of output, the USB-C Charger Cord can fast-charge a smartphone or tablet. To use, connect the cable from a USB-C device to a USB-A wall charger.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Convenient 10-pack facilitates multiple installations
- Charge and sync a USB-C device from an available USB-A port on a laptop or desktop computer
- Charge your USB-C devices using a USB-A wall charger, car charger or power bank

Merkmale

- **PRACTICAL 10 PACK:** USB-A to Type-C cable delivers 3A output for fast charging portable USB-C devices; Use this 10-pack to facilitate multiple connections; Connect to a USB-A wall charger, power bank, or charge/access your phone/tablet from a USB-A host
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Use this 10-Pack to enable additional connections without swapping cables; Ideal for fast charging USB-C smartphones/tablets; Supports USB 2.0 for file transfer and device synchronization when connected to a USB-A host or external storage
- **PERFORMANCE:** Supports 15W/3A Fast Charge; USB 2.0 (480Mbps); Length: 6-foot (1.8-meter); Color: Black; O.D.: 0.14in (3.5mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **COMPATIBILITY:** Compatible with a wide range of USB-C devices including iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Google Pixel, USB-C portable monitors Asus ZenScreen/ProArt, iPad Pro, MacBook Air/Pro, Surface Book, and more

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	TPE - Thermoplastic Elastomers
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

MTBF	Rated over 10,000 insertion cycles
------	------------------------------------

Steckverbinder	Steckverbinder A	1 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
	Steckverbinder B	1 - USB 2.0 Type-C
Spezielle Hinweise/Anforderungen	Hinweis	Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)
Strom	Power Delivery	15W
	Eingangsstrom	3A
Umgebungsbedingungen	Betriebstemperatur	-10 to 60 (14°F to 140°F)
	Lagertemperatur	-20 to 70 (-4°F to 158°F)
	Feuchtigkeit	5%~85%
Physische Eigenschaften	Farbe	Schwarz
	Steckverbinderart	Gerade
	Drahtstärke	22/30 AWG
	Gehäusetyp	Polyamide Resin
	Kabellänge	6.0 ft [1.8 m]
	Außendurchmesser des Kabels	0.1 in [3.5 mm]
	Produktlänge	6.1 ft [1.8 m]
	Produktbreite	0.5 in [1.2 cm]
	Produktgröße	0.2 in [6.3 mm]
	Produktgewicht	1.4 oz [40 g]

Verpackungsinformationen

Paketmenge	10
Paketlänge	9.9 in [25.2 cm]
Paketbreite	13.0 in [33.0 cm]
Pakethöhe	2.0 in [5.0 cm]
Versandgewicht (Verpackung)	14.4 oz [408.0 g]

Verpackungsinhalt

Im Paket enthalten	10 - 1,8m USB-C Kabel - M/M
--------------------	-----------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.