

USB-C to USB-C Cable w/ 5A PD - M/M - 2 m (6 ft.) - USB 2.0 - USB-IF Certified

Product ID: USB2C5C2M



With up to 5A (100W) of power output, you can use this USB-C to USB-C cable to power and charge a USB-C laptop, such as your Apple MacBook Pro, MacBook or Chromebook Pixel, using a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

The 5A of Power Delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable, which is perfect for people on the move. Decrease your charge times and make sure your mobile devices are ready, whenever you need them while you're on the road.

The USB Type-C cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB2C5C2M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your USB-C laptop from a charger or power bank
- Charge your USB-C laptop from a docking station
- Fast charge your USB-C mobile devices from a charger
- Sync your USB-C mobile devices with a laptop

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)	Connector A	USB Type-C (24-pin) USB 2.0 (480Mbps)
	Connector B	USB Type-C (24-pin) USB 2.0 (480Mbps)
Power	Power Delivery	100W
Environmental	Operating Temperature	0C to 35C (32F to 95F)
	Storage Temperature	-10C to 80C (14F to 176F)
	Humidity	5%-80% RH (no condensation)
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	24/26 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2.0 m]
	Product Width	0.5 in [12.000 mm]
	Product Height	0.2 in [6.000 mm]
	Weight of Product	3.8 oz [108.000 g]
Packaging Information	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.0 in [0.700 mm]
	Shipping (Package) Weight	4.1 oz [116.000 g]
What's in the Box	Included in Package	USB-C cable

****Product appearance and specifications are subject to change without notice.***

