

13ft (4m) USB-C Fast Charging Cable, Charge & Sync, 100W (5A) PD, USB 2.0, USB-IF Certified - Black USB C Charging Cord

Product ID: USB2C5C4M



This USB-C cable with USB Power Delivery lets you power USB Type-C devices from your USB-C laptop or charge your USB-C laptop from a USB-C wall charger.

With up to 5A (100W) of power output, you can use this USB Type-C cable to power and charge a USB-C laptop, such as your Apple MacBook or Chromebook Pixel, using a USB-C wall charger, car charger or power bank.

The 5A of power delivery lets you charge your mobile devices faster than with a regular USB-C 2.0 cable. The cable is perfect for people on the move - decrease your charge times and make sure your mobile devices are ready, whenever you need them, while you're on the road.

The non-standard 4-meter cable gives you the extra length you need to overcome distance restrictions and stay connected. You can charge and sync your USB-C mobile device, in almost any environment. Even while you're taking notes in a boardroom, catching up on emails in your hotel room, or reading in a coffee shop, the connection to your mobile device will reach your computer or wall charger more comfortably.

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 2.0 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

Certifications, Reports and Compatibility



Applications

- Power your USB-C laptop from a USB Type-C wall charger, car charger or power bank
- Charge your USB Type-C laptop from a your docking station
- Fast charge your USB-C mobile devices from your USB-C laptop or wall charger
- Sync your USB-C mobile devices with your USB-C computer

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast charging your mobile devices, or powering your USB-C laptop
- Offers 4 meters in cable length
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty
- Please note that this USB 2.0 cable does not support any video; For connecting or extending USB-C Displays/Monitors we recommend our USB-C 3.0 cables (e.g. USB315CCV2M)

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	100W
----------------	------

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)

Humidity 5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/26 AWG
Cable Length	13.1 ft [4 m]
Product Length	13.1 ft [4.0 m]
Product Width	0.2 in [6.0 mm]
Product Height	0.2 in [4.0 mm]
Weight of Product	7.7 oz [219.0 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.6 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	7.8 oz [222.0 g]

What's in the Box

Included in Package	1 - USB-C cable
---------------------	-----------------

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***