

## 6.6ft (2m) USB-C Charging Cable, Charge & Sync, 60W (3A) PD, USB 2.0 Laptop Charger Cable - White USB C Charging Cord

**Product ID:** USB2CC2MNCWHE



Seamlessly charge a USB Type-C mobile device or transfer files to a USB-C host computer with this high-quality USB-C cable. The USB-C charger cord facilitates up to 60W Power Delivery and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent charging, the USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 2-meter (6.6-foot) USB Type-C cable is the ideal length for desk workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

With up to 3A of output, the USB-C Charger Cord supports up to 60W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

### Certifications, Reports and Compatibility



### Applications

- Charge and sync a USB-C device from an available USB-C port on a laptop or desktop computer
- Charge your USB-C devices using a USB-C wall charger, car charger or power bank

## Features

- **USB TYPE-C CHARGING CABLE:** High quality USB-C to C cable delivers 3A output for fast charging USB-C laptops and mobile devices; Connects to a USB-C wall charger or power bank; Supports up to 60W USB Power Delivery 2.0
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Universal compatibility with USB-C PD-enabled devices; Supports USB 2.0 for general use, including file transfer and device synchronization when connected to a USB-C host computer or external storage
- **PERFORMANCE:** 2-meter (6.6-foot); 60W/3A Power Delivery 2.0; USB 480Mbps; Color: White; O.D.: 0.14in (3.5mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB-C charging cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This USB Type-C cable is available in other lengths

### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

### Performance

|      |                                    |
|------|------------------------------------|
| MTBF | Rated over 10,000 insertion cycles |
|------|------------------------------------|

### Connector(s)

|             |                    |
|-------------|--------------------|
| Connector A | 1 - USB 2.0 Type-C |
| Connector B | 1 - USB 2.0 Type-C |

### Special Notes / Requirements

|      |                                                                      |
|------|----------------------------------------------------------------------|
| Note | Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode) |
|------|----------------------------------------------------------------------|

### Power

|                |             |
|----------------|-------------|
| Power Source   | USB-Powered |
| Power Delivery | 60W         |
| Input Current  | 3A          |

---

#### Environmental

|                       |                                 |
|-----------------------|---------------------------------|
| Operating Temperature | -10 to 60 (14&degF to 140&degF) |
| Storage Temperature   | -20 to 70 (-4&degF to 158&degF) |
| Humidity              | 5%~85%                          |

---

#### Physical Characteristics

|                   |                 |
|-------------------|-----------------|
| Color             | White           |
| Connector Style   | Straight        |
| Wire Gauge        | 24/30 AWG       |
| Material          | Polyamide Resin |
| Cable Length      | 6.6 ft [2 m]    |
| Cable OD          | 0.1 in [3.5 mm] |
| Product Length    | 6.6 ft [2.0 m]  |
| Product Width     | 0.5 in [1.2 cm] |
| Product Height    | 0.2 in [6.3 mm] |
| Weight of Product | 1.7 oz [49.0 g] |

---

#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Length            | 6.5 in [16.6 cm] |
| Package Width             | 5.0 in [12.7 cm] |
| Package Height            | 0.6 in [1.5 cm]  |
| Shipping (Package) Weight | 1.8 oz [50.0 g]  |

---

#### What's in the Box

|                     |                       |
|---------------------|-----------------------|
| Included in Package | 1 - USB-C Cable - M/M |
|---------------------|-----------------------|

---

#### Warranty Information

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

*\*Product appearance and specifications are subject to change without notice.*