

6ft (1.8m) USB-C Charging Cable, 60W (3A) PD, Dual-Layer Braided Nylon/TPE Jacket, Rugged USB C Charging Cord, USB 2.0 Laptop Charger Cable

Product ID: USB2CC6FNCBR



Connect a charger or hub to a USB PD-enabled device using this Rugged USB-C Cable, delivering up to 60W Power Delivery and 3A output for fast charging. Clear markings on each connector eliminate confusion, helping you identify the right cable instantly. No more guesswork with lookalike or unmarked USB-C cords.

Rugged and Flexible

The USB-C Charging Cable features a TPE inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 10,000 insertion cycles.

Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 6-foot (1.8-meter) USB Type-C cable is the ideal length for large desk and mobile workstations where extra reach is desired.

Power a Laptop

With up to 3A of output, the USB-C Charger Cord supports up to 60W of Power Delivery to charge a USB-C laptop or fast-charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility



Applications

Features

- **USB-C CHARGING CABLE:** High quality USB-C cable delivers up to 60W/3A Power Delivery for fast charging USB-C laptops and mobile devices; Connects to a USB-C wall charger or power bank; Performance markings on connectors for easy identification
- **QUALITY CONSTRUCTION:** Dual-layer jacket incorporates a TPE inner layer for optimal flexibility and a braided nylon exterior for rugged use; Designed to withstand frequent $\pm 90^\circ$ bends; Nickel-plated connectors rated beyond 10,000 insertions
- **APPLICATIONS:** Universal compatibility with USB-C PD-enabled devices; Supports USB 2.0 for general file transfer and device synchronization when connected to a USB-C host computer or external storage
- **PERFORMANCE:** 6-foot (1.8-meter); 60W/3A Power Delivery 2.0; USB 480Mbps; Color: Black; 23/28AWG; O.D.: 0.18in (4.5mm); Dual-layer TPE Jacket with Braided Nylon; NOTE: USB-C video (DP Alt Mode) is not supported
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB-C charging cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This USB Type-C cable is available in other lengths

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	TPE with Braided Nylon

Performance

MTBF	Rated beyond 10,000 insertions
------	--------------------------------

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	60W
Input Current	3A

Environmental

Operating Temperature	-20 to 40 (-4°F to 104°F)
Storage Temperature	-20 to 70 (-4°F to 158°F)
Humidity	30%~70%

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	23/28 AWG
Material	PE
Cable Length	6.0 ft [1.8 m]
Cable OD	0.2 in [4.5 mm]
Product Length	6.0 ft [1.8 m]
Product Width	0.4 in [11.2 mm]
Product Height	0.3 in [6.5 mm]
Weight of Product	2.0 oz [58 g]

Packaging Information

Package Length	5.1 in [13.0 cm]
Package Width	5.5 in [14.0 cm]
Package Height	0.7 in [1.8 cm]
Shipping (Package) Weight	3.1 oz [88.0 g]

What's in the Box

Included in Package	1 - Braided USB-C Cable - Black
---------------------	---------------------------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*