

6ft (1.8m) USB-C Charging Cable, Charge & Sync, 60W (3A) PD, USB 2.0 Laptop Charger Cable, TPE Jacket - White USB C Charging Cord

Produkt-ID: USB2CC6FWHE



Seamlessly charge a USB Type-C mobile device or transfer files to a USB-C host computer with this high-quality USB-C cable. The USB-C charger cord facilitates up to 60W Power Delivery and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent charging, the USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 3ft (0.9m) USB Type-C cable is the ideal length for desk workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

With up to 3A of output, the USB-C Charger Cord supports up to 60W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Charge and sync a USB-C device from an available USB-C port on a laptop or desktop computer

- Charge your USB-C devices using a USB-C wall charger, car charger or power bank

Merkmale

- **USB TYPE-C CHARGING CABLE:** High quality USB-C to C cable delivers 3A output for fast charging USB-C laptops and mobile devices; Connects to a USB-C wall charger or power bank; Supports up to 60W USB Power Delivery 2.0
- **HOCHWERTIGE KONSTRUKTION:** Vernickelte Stecker, für mindestens 10.000 Einsteckzyklen; robuste Zugentlastungen mit 8mm Biegeradius; strapazierfähiger TPE-Außenmantel, ungiftig, halogenfrei und RoHS-konform; Aluminiumgeflecht Abschirmung für hohen EMI-Schutz
- **APPLICATIONS:** Universal compatibility with USB-C PD-enabled devices; Supports USB 2.0 for file transfer and device synchronization when connected to a USB-C host or external storage
- **PERFORMANCE:** 6-foot (1.8-meter); 60W/3A Power Delivery 2.0; USB 480Mbps; Color: White; O.D.: 0.14in (3.5mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this USB-C charging cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This USB Type-C cable is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	TPE - Thermoplastic Elastomers
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

MTBF	Rated over 10,000 insertion cycles
------	------------------------------------

Steckverbinder

Steckverbinder A	1 - USB 2.0 Type-C
Steckverbinder B	1 - USB 2.0 Type-C

Strom

Stromversorgung	USB-betrieben
Power Delivery	60W
Eingangsspannung	5V DC, 9V DC, 12V DC, 15V DC, 20V DC
Eingangsstrom	3A

Umgebungsbedingungen

Betriebstemperatur	-10 to 60 (14°F to 140°F)
Lagertemperatur	-20 to 70 (-4°F to 158°F)
Feuchtigkeit	5%~85%

Physische Eigenschaften

Farbe	Weiß
Steckverbinderart	Gerade
Drahtstärke	24/30 AWG
Gehäusety	Polyamide Resin
Kabellänge	3.3 ft [1 m]
Außendurchmesser des Kabels	0.1 in [3.5 mm]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	0.5 in [1.2 cm]
Produkt	0.2 in [6.3 mm]
Produktgewicht	2.2 oz [62 g]

Verpackungsinformationen

Paketlänge	5.2 in [13.3 cm]
Paketbreite	5.0 in [12.7 cm]
Pakethöhe	0.6 in [1.5 cm]

Versandgewicht (Verpackung)	1.8 oz [52.0 g]
--------------------------------	-----------------

Verpackungsinhalt

Im Paket enthalten	2 - 6ft USB-C Kabel - M/M
--------------------	---------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.