

Professional USB to DVI External Dual or Multi Monitor Video Adapter

Product ID: USB2DVIPRO



The USB2DVIPRO Professional USB DVI External Dual or Multi Monitor Video Adapter is the perfect solution for turning your workstation into a dual or multi-monitor environment using your USB ports - providing high quality dual display or multi-monitor capability for a variety of laptop or desktop applications.

With improved performance compared to our USB2DVI, this USB DVI-D display adapter is capable of running up to five additional displays from one computer simultaneously (using four USB2DVIPRO External Multi Monitor Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external DVI-D video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

USB2DVIPRO offers support for Microsoft Windows (including Aero themes) and Mac OS X, and with support for resolutions up to 1920x1200 this device is ideal for larger displays / monitors.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Can't install a new or additional video card? No problem, the USB2DVIPRO uses USB ports to add DVI connectivity to your PC or Mac
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIPRO device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different screens; check your email on one display while editing a document on the other

- Use the adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Support for Aero themes in Windows
- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- USB Powered - No external power adapter required
- Works with MAC OS X
- Connect up to five adapters to one PC for a true extended desktop experience
- Quick and easy to install

Hardware

Warranty	2 Years
AV Input	USB 2.0
AV Output	DVI
USB Pass-Through	No
Memory	16MB
Chipset ID	DisplayLink - DL-195

Performance

Maximum Digital Resolutions	1920x1200 (32-bit color)
Supported Resolutions	Widescreen (16/32 bit): 1920x1200, 1680x1050, 1440x900, 1366x768 Standard (16/32 bit): 1600x1200, 1280x1024, 1024x768, 800x600, 640x480
MTBF	621,445 Hours



Connector(s)

Connector Type(s)	DVI-I (29 pin)
	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8/8.1, 10
	macOS 10.6 - 10.11, 11.0
	Chrome OS v51
	Ubuntu 14.04, 16.04, 18.04

Special Notes / Requirements

System and Cable Requirements	System Processor: 1.2GHz
	System Memory: 512MB
Note	Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported
	This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic
	Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources
	This USB video adapter is not intended for graphical intensive applications, such as gaming

Indicators

LED Indicators	Blue - Power
----------------	--------------

Physical Characteristics

Color	Black
Product Length	3.5 in [90 mm]
Product Width	1.9 in [48 mm]
Product Height	0.9 in [23.5 mm]
Weight of Product	2.6 oz [73 g]



**Packaging
Information**

Package Length	6.4 in [16.3 cm]
Package Width	2.5 in [62.5 mm]
Package Height	5.7 in [14.4 cm]
Shipping (Package) Weight	8.8 oz [250 g]

**What's in the
Box**

Included in Package	Driver CD
	Instruction Manual
	USB to DVI Adapter

****Product appearance and specifications are subject to change without notice.***

