

10 ft USB 2.0 Certified A to B Cable - M/M

Product ID: USB2HAB10



The USB2HAB10 10ft USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

Features

- USB-IF Certified Hi-Speed USB 2.0 (480 Mbps)
- Supports USB 2.0 data transfer rates up to 480 Mbps

Hardware

Warranty

Lifetime

Connector Plating	Nickel
-------------------	--------

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
-------------	----------------------------

Connector B	USB B (4 pin)
-------------	---------------

Physical Characteristics

Color	Black
-------	-------

Wire Gauge	22/28 AWG
------------	-----------

Cable Length	10.0 ft [3.0 m]
--------------	-----------------

Product Length	10.0 ft [3.0 m]
----------------	-----------------

Product Width	0.0 in [0.0 mm]
---------------	-----------------

Product Height	0.0 in [0.0 mm]
----------------	-----------------

Weight of Product	4.7 oz [133.3 g]
-------------------	------------------

Packaging Information

Package Length	8.7 in [22.0 cm]
----------------	------------------

Package Width	4.7 in [12.0 cm]
---------------	------------------

Package Height	0.8 in [20.0 mm]
----------------	------------------

Shipping (Package) Weight	4.7 oz [134.3 g]
---------------------------	------------------

What's in the Box

Included in Package	10 ft USB 2.0 Certified A to B Cable - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***

