

## 0.5m USB 2.0 A to B Cable - M/M

Product ID: USB2HAB50CM



The USB2HAB50CM 0.5-meter USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

### Features

- High quality USB 'A' and USB 'B' connectors
- Supports USB 2.0 data transfer rates up to 480 Mbps

---

Hardware	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid

<b>Connector(s)</b>	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	USB B (4 pin)
<b>Environmental</b>	Operating Temperature	-10~40
	Storage Temperature	-10~40
	Humidity	10%~90%
<b>Physical Characteristics</b>	Color	Black
	Wire Gauge	24/28 AWG
	Cable Length	19.7 in [5 cm]
	Product Length	19.7 in [5.0 cm]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	1.3 oz [35.500 g]
<b>Packaging Information</b>	Package Quantity	1
	Package Length	8.7 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.4 in [10.000 mm]
	Shipping (Package) Weight	1.3 oz [36.500 g]
<b>What's in the Box</b>	Included in Package	0.5 m USB 2.0 A to B Cable - M/M

*\*Product appearance and specifications are subject to change without notice.*

