

6 ft USB 2.0 Certified A to B Cable - M/M

Product ID: USB2HAB6



The USB2HAB6 6ft USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

Features

- High quality USB 'A' and USB 'B' connectors
- Supports USB 2.0 data transfer rates up to 480 Mbps

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB B (4 pin)

Physical Characteristics

Color	Black
Wire Gauge	24/28 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.2 in [4.8 mm]
Product Length	6.0 ft [1.8 m]
Product Width	0.6 in [1.5 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	3.1 oz [88.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	5.1 in [13.0 cm]
Package Height	0.4 in [1.1 cm]
Shipping (Package) Weight	3.3 oz [94.0 g]

What's in the Box

Included in Package	1 - 6 ft USB 2.0 A to B Cable - M/M
---------------------	-------------------------------------

****Product appearance and specifications are subject to change without notice.***