

USB to 5.5mm Power Cable - Type M Barrel - 2m

Produkt ID: USB2TYPEM2M

Tired of having to carry around a separate wall adapter in order to power or charge your 5V devices, such as certain external hard drives, streaming media players, and Bluetooth® speakers?

This 2m USB power cable makes it easier to power 5V DC devices that have a Type M (OD: 5.5mm, ID:2.1mm) barrel power connector. You can power or charge the devices through an available USB port on your laptop or desktop computer.

Expertly designed and constructed of high-quality materials, the StarTech.com USB2TYPEM2M power cable is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Power your external hard drive or other devices that are equipped with a Type-M power connector through an available USB port on your computer
- Charge your Bluetooth speakers and other chargeable devices through an available USB port on your computer

Funktioner


- Aluminum-mylar foil with braided shielding
- Molded connectors with strain relief
- Durable PVC construction

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	USB Type-A (4-stifts) USB 2.0
-------------	-------------------------------



Connector B Cylindrisk strömkontakt (storlek M, OD: 5,50, ID: 2,10)

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-10°C to 30°C (14°F to 86°F)
Luftfuktighet	30%-75% RH

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.0 ft [1.8 m]
Produktbredd	0.6 in [15.0 mm]
Produkt höjd	0.4 in [10.0 mm]
Produktvikt	1.6 oz [45.0 g]

Förpackning

Förpackningsantal	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Fraktvikt (förpackning)	1.8 oz [51.0 g]

Vad det är i lådan

Ingår i paketet	2 m USB to Type M Barrel 5V DC Power Cable
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

