

## USB VGA External Dual or Multi Monitor Video Adapter - High Resolution

Produkt ID: USB2VGA2



The USB2VGA2 USB VGA Adapter turns an available USB 2.0 port into an external video card VGA port - providing high quality dual-display or multi-monitor capability that can be used in a variety of laptop or desktop applications to increase your productivity.

The device also offers the option of running up to five additional displays simultaneously (using five USB2VGA2 Multi Monitor External Video Cards). Each connected adapter can be used to further extend the desktop or mirror the image shown on the existing display - all without having to open the computer case to install an additional video card.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifikat, rapporter och kompatibilitet

### Användning

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGA2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display

- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

## Funktioner

- Optimal performance at 1680x1050 and ideal for use with 20" to 22" monitors or smaller
- Easy installation
- No power adapter required

---

### Hårdvara

Garantipolicy	2 Years
AV-ingång	USB 2.0
AV-utgång	VGA
USB-passthrough	Nej
Minne	16MB
Chipset-ID	SiS - 315

---

### Prestanda

Stödda upplösningar	Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
	Widescreen(16 bit): 1920x1200, 1920x1080
	(16/32 bit): 1680x1050, 1440x900, 1280x800, 1280x768

---

### Kontakt(er)



Kontakttyp(er)	USB Type-A (4-stifts) USB 2.0 VGA (15-stifts, High Density D-Sub)
----------------	--

---

Mjukvara

OS-kompatibilitet	Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)
-------------------	--

---

Särskilda  
anmärkningar/krav

System- och kabelkrav	System Processor: Quad Core 2.4GHz (i5 recommended) System Memory: 4GB
-----------------------	---

Obs. This USB video adapter uses an SiS family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink®, Trigger or Fresco Logic®

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

---

Utseende

Kabinettyp	Av plast
Kabellängd	18.0 in [45.7 cm]
Produktlängd	4.3 in [11 cm]
Produktbredd	2.0 in [51 mm]
Produkt höjd	0.9 in [24 mm]
Produktvikt	3.2 oz [90 g]

---

Förpackning

Package Length	6.0 in [15.2 cm]
Package Width	2.3 in [58 mm]
Package Height	9.0 in [22.8 cm]
Fraktvikt (förpackning)	10.2 oz [290 g]



---

Vad det är i lådan

Ingår i paketet

USB to VGA Adapter

Driver CD

Instruction Manual

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

